

Varistar 主机托管机柜, RAL 7021



带 2、3 或 4 个分隔单元的主机托管机柜，RAL 7021，用于容纳服务器，同时将隔间接入与布线分开。

认证



功能

带隔间的主机托管机柜

灵活的布线，可从上方、下方、左侧或右侧接入线缆（数据线和电源线可分开走线）

多点门锁

网门

防护等级 IP 20

颜色 RAL 7021（黑灰色）

技术参数

产品类型： 机架

框架材料： 钢

Table 1/3

物料号	机架高度	高度	覆层材料	框架颜色	宽度	框架颜色代码
-----	------	----	------	------	----	--------

10130-202	40U	2000mm	钢	暗灰色	600mm	RAL 7021
10130-203	39U	2000mm	钢	暗灰色	600mm	RAL 7021
10130-204	40U	2000mm	钢	暗灰色	600mm	RAL 7021
10130-205	40U	2000mm	钢	暗灰色	800mm	RAL 7021
10130-206	39U	2000mm	钢	暗灰色	800mm	RAL 7021
10130-207	40U	2000mm	钢	暗灰色	800mm	RAL 7021
10130-208	44U	2200mm	钢	暗灰色	600mm	RAL 7021
10130-209	45U	2200mm	钢	暗灰色	600mm	RAL 7021
10130-210	44U	2200mm	钢	暗灰色	600mm	RAL 7021
10130-211	44U	2200mm	钢	暗灰色	800mm	RAL 7021
10130-212	45U	2200mm	钢	暗灰色	800mm	RAL 7021
10130-213	44U	2200mm	钢	暗灰色	800mm	RAL 7021
10130-214	40U	2000mm	钢	暗灰色	600mm	RAL 7021
10130-215	39U	2000mm	钢	暗灰色	600mm	RAL 7021
10130-216	40U	2000mm	钢	暗灰色	600mm	RAL 7021
10130-217	40U	2000mm	钢	暗灰色	800mm	RAL 7021
10130-218	39U	2000mm	钢	暗灰色	800mm	RAL 7021

10130-219	40U	2000mm	钢	暗灰色	800mm	RAL 7021
10130-220	44U	2200mm	钢	暗灰色	600mm	RAL 7021
10130-221	45U	2200mm	钢	暗灰色	600mm	RAL 7021
10130-222	44U	2200mm	钢	暗灰色	600mm	RAL 7021
10130-223	44U	2200mm	钢	暗灰色	800mm	RAL 7021
10130-224	45U	2200mm	钢	暗灰色	800mm	RAL 7021
10130-225	44U	2200mm	钢	暗灰色	800mm	RAL 7021
10130-257	45U	2450mm	钢	暗灰色	600mm	RAL 7021
10130-258	48U	2450mm	钢	暗灰色	600mm	RAL 7021
10130-259	48U	2450mm	钢	暗灰色	600mm	RAL 7021
10130-260	45U	2450mm	钢	暗灰色	800mm	RAL 7021
10130-261	48U	2450mm	钢	暗灰色	800mm	RAL 7021
10130-262	48U	2450mm	钢	暗灰色	800mm	RAL 7021
10130-269	45U	2450mm	钢	暗灰色	600mm	RAL 7021
10130-270	48U	2450mm	钢	暗灰色	600mm	RAL 7021
10130-271	48U	2450mm	钢	暗灰色	600mm	RAL 7021
10130-272	45U	2450mm	钢	暗灰色	800mm	RAL 7021

10130-273	48U	2450mm	钢	暗灰色	800mm	RAL 7021
10130-274	48U	2450mm	钢	暗灰色	800mm	RAL 7021

Table 2/3						
物料号	覆层颜色	覆层颜色代码	深度	包装数量	隔间数量	完成
10130-202	暗灰色	RAL 7021	1000mm	1	2	粉末涂层
10130-203	暗灰色	RAL 7021	1000mm	1	3	粉末涂层
10130-204	暗灰色	RAL 7021	1000mm	1	4	粉末涂层
10130-205	暗灰色	RAL 7021	1000mm	1	2	粉末涂层
10130-206	暗灰色	RAL 7021	1000mm	1	3	粉末涂层
10130-207	暗灰色	RAL 7021	1000mm	1	4	粉末涂层
10130-208	暗灰色	RAL 7021	1000mm	1	2	粉末涂层
10130-209	暗灰色	RAL 7021	1000mm	1	3	粉末涂层
10130-210	暗灰色	RAL 7021	1000mm	1	4	粉末涂层
10130-211	暗灰色	RAL 7021	1000mm	1	2	粉末涂层
10130-212	暗灰色	RAL 7021	1000mm	1	3	粉末涂层
10130-213	暗灰色	RAL 7021	1000mm	1	4	粉末涂层
10130-214	暗灰色	RAL 7021	1200mm	1	2	粉末涂层
10130-215	暗灰色	RAL 7021	1200mm	1	3	粉末涂层

物料号	覆层颜色	覆层颜色代码	深度	包装数量	隔间数量	完成
10130-216	暗灰色	RAL 7021	1200mm	1	4	粉末涂层
10130-217	暗灰色	RAL 7021	1200mm	1	2	粉末涂层
10130-218	暗灰色	RAL 7021	1200mm	1	3	粉末涂层
10130-219	暗灰色	RAL 7021	1200mm	1	4	粉末涂层
10130-220	暗灰色	RAL 7021	1200mm	1	2	粉末涂层
10130-221	暗灰色	RAL 7021	1200mm	1	3	粉末涂层
10130-222	暗灰色	RAL 7021	1200mm	1	4	粉末涂层
10130-223	暗灰色	RAL 7021	1200mm	1	2	粉末涂层
10130-224	暗灰色	RAL 7021	1200mm	1	3	粉末涂层
10130-225	暗灰色	RAL 7021	1200mm	1	4	粉末涂层
10130-257	暗灰色	RAL 7021	1000mm	1	2	粉末涂层
10130-258	暗灰色	RAL 7021	1000mm	1	3	粉末涂层
10130-259	暗灰色	RAL 7021	1000mm	1	4	粉末涂层
10130-260	暗灰色	RAL 7021	1000mm	1	2	粉末涂层
10130-261	暗灰色	RAL 7021	1000mm	1	3	粉末涂层
10130-262	暗灰色	RAL 7021	1000mm	1	4	粉末涂层
10130-269	暗灰色	RAL 7021	1200mm	1	2	粉末涂层

物料号	覆层颜色	覆层颜色代码	深度	包装数量	隔间数量	完成
10130-270	暗灰色	RAL 7021	1200mm	1	3	粉末涂层
10130-271	暗灰色	RAL 7021	1200mm	1	4	粉末涂层
10130-272	暗灰色	RAL 7021	1200mm	1	2	粉末涂层
10130-273	暗灰色	RAL 7021	1200mm	1	3	粉末涂层
10130-274	暗灰色	RAL 7021	1200mm	1	4	粉末涂层

Table 3/3			
物料号	材料	静态负载	快速发货
10130-202	钢	800kg	No
10130-203	钢	800kg	No
10130-204	钢	800kg	No
10130-205	钢	800kg	No
10130-206	钢	800kg	No
10130-207	钢	800kg	No
10130-208	钢	800kg	No
10130-209	钢	800kg	No
10130-210	钢	800kg	No
10130-211	钢	800kg	No

物料号	材料	静态负载	快速发货
10130-212	钢	800kg	No
10130-213	钢	800kg	No
10130-214	钢	800kg	No
10130-215	钢	800kg	No
10130-216	钢	800kg	No
10130-217	钢	800kg	No
10130-218	钢	800kg	No
10130-219	钢	800kg	No
10130-220	钢	800kg	No
10130-221	钢	800kg	No
10130-222	钢	800kg	No
10130-223	钢	800kg	No
10130-224	钢	800kg	No
10130-225	钢	800kg	No
10130-257	钢	800kg	No
10130-258	钢	800kg	No
10130-259	钢	800kg	No

物料号	材料	静态负载	快速发货
10130-260	钢	800kg	No
10130-261	钢	800kg	No
10130-262	钢	800kg	No
10130-269	钢	800kg	No
10130-270	钢	800kg	No
10130-271	钢	800kg	No
10130-272	钢	800kg	No
10130-273	钢	800kg	No
10130-274	钢	800kg	No

其他产品详情

侧面板必须单独订购。要选择合适的电缆面板，请参阅附件。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



我们强大的品牌组合:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE