

Varistar CP 空气分隔挡盖, 宽度 800 mm



适用于 800 mm 宽机柜的填充板（普通面板），用于避免前至后冷却机架中发生空气循环。

功能

空气分隔, 适用于 800 mm 宽机柜的盖板

网络机柜和服务器机柜可并排安装

密封条, UL 94 HF-1, -20 °C ... 100° C

封闭构件

盖板可防止不必要的空气串扰, 例如, 不希望热废气和传入的冷空气混合

只与重负载横杆兼容, 与复位支架不兼容

技术参数

产品类型: 机柜/机架面板

材料: 钢

Table 1/2

物料号	机架高度	高度	包装数量	颜色	颜色代码	完成
21630-141	42U	2000mm	1	暗灰色	RAL 7021	粉末涂层
21630-143	52U	2450mm	1	暗灰色	RAL 7021	粉末涂层
21630-142	47U	2200mm	1	暗灰色	RAL 7021	粉末涂层

Table 2/2				
物料号	防护等级	类型	宽度	快速发货
21630-141	IP20	盲板	800mm	No
21630-143	IP20	盲板	800mm	No
21630-142	IP20	盲板	800mm	No

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE