

Varistar CP 双钢门, 平板型, 3 点锁定



Varistar CP 钢制双门，带 3 点锁定和 2 个门铰链，适用于 IP 20 防护等级应用。

功能

带 IP 20 防护等级 3 点锁的双钢门

杆式把手，带钥匙锁芯（2 把钥匙）

开门角度 180°

标准配件, 右门锁

可使用摇柄把手 24630003 和带钥匙或按钮的 DIN 半圆形锁芯进行改装

技术参数

锁定类型: 3 点锁定

产品类型: 机柜门

防护等级: IP20

材料: 钢

Table 1/2

物料号	机架高度	高度	宽度	包装数量	颜色	颜色代码
21630-440	24U	1200mm	600mm	1	暗灰色	RAL 7021
21630-441	24U	1200mm	800mm	1	暗灰色	RAL 7021
21630-442	29U	1400mm	600mm	1	暗灰色	RAL 7021

物料号	机架高度	高度	宽度	包装数量	颜色	颜色代码
21630-443	29U	1400mm	800mm	1	暗灰色	RAL 7021
21630-444	33U	1600mm	600mm	1	暗灰色	RAL 7021
21630-445	33U	1600mm	800mm	1	暗灰色	RAL 7021
21630-446	38U	1800mm	600mm	1	暗灰色	RAL 7021
21630-447	38U	1800mm	800mm	1	暗灰色	RAL 7021
21630-086	42U	2000mm	600mm	1	暗灰色	RAL 7021
21630-089	42U	2000mm	800mm	1	暗灰色	RAL 7021
21630-087	47U	2200mm	600mm	1	暗灰色	RAL 7021
21630-090	47U	2200mm	800mm	1	暗灰色	RAL 7021
21630-088	52U	2450mm	600mm	1	暗灰色	RAL 7021
21630-091	52U	2450mm	800mm	1	暗灰色	RAL 7021

Table 2/2					
物料号	符合	完成	类型	搭配	快速发货
21630-440	IEC 61587-1, IEC 61587-3	粉末涂层	钢制双门	Varistar CP	No
21630-441	IEC 61587-1, IEC 61587-3	粉末涂层	钢制双门	Varistar CP	No
21630-442	IEC 61587-1, IEC 61587-3	粉末涂层	钢制双门	Varistar CP	No
21630-443	IEC 61587-1, IEC 61587-3	粉末涂层	钢制双门	Varistar CP	No

物料号	符合	完成	类型	搭配	快速发货
21630-444	IEC 61587-1, IEC 61587-3	粉末涂层	钢制双门	Varistar CP	No
21630-445	IEC 61587-1, IEC 61587-3	粉末涂层	钢制双门	Varistar CP	No
21630-446	IEC 61587-1, IEC 61587-3	粉末涂层	钢制双门	Varistar CP	No
21630-447	IEC 61587-1, IEC 61587-3	粉末涂层	钢制双门	Varistar CP	No
21630-086	IEC 61587-1, IEC 61587-3	粉末涂层	钢制双门	Varistar CP	No
21630-089	IEC 61587-1, IEC 61587-3	粉末涂层	钢制双门	Varistar CP	No
21630-087	IEC 61587-1, IEC 61587-3	粉末涂层	钢制双门	Varistar CP	No
21630-090	IEC 61587-1, IEC 61587-3	粉末涂层	钢制双门	Varistar CP	No
21630-088	IEC 61587-1, IEC 61587-3	粉末涂层	钢制双门	Varistar CP	No
21630-091	IEC 61587-1, IEC 61587-3	粉末涂层	钢制双门	Varistar CP	No

其他产品详情

24U - 33U IP20 门配有 2 个铰链，38U - 52U IP20 门配有 3 个铰链，以确保较高机柜的坚固 IP20 关闭结构

如需更换 1333 DIN 锁杠杆式把手，请单独订购杠杆式把手 24630003 和 DIN 锁

请单独购买接地套件。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



我们强大的品牌组合:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE