

Varistar CP EMC Cabinet, IP 55



Varistar: Highly versatile, robust welded steel frame electronics cabinet with a wide range of available features including protection against dust and water (IP 20 and IP 55), cooling options from fans to 40kW air-to-water chillers, shock, vibration and seismic resistance up to NEBS GR-63-CORE Bellcore zone 4 and industry leading radio-frequency/electromagnetic (RFI / EMI) shielding of 60 dB at 1 GHz, 40 dB at 3 GHz (tested to IEC 61587-3).

功能

屏蔽能力：1 GHz, 60 dB, 3 GHz, 40 dB（经测试符合 IEC 61587 - 3 标准）

18 GHz 时屏蔽 30 dB，（经测试符合 EN 61000-5-7 标准），带符合 EN45545 标准的垫片

防护类型 IP 55

静态承载能力：1600 千克

含 4 点锁的机柜门和螺钉固定的侧板

侧面板和后面板可由一人安装

技术参数

静态负载:	1600kg
产品类型:	机柜
防护等级:	IP55
覆层颜色代码:	RAL 7021
框架材料:	钢

Table 1/3

物料号	机架高度	高度	框架颜色	宽度	框架颜色代码	电缆入口
10630-044	42U	2000mm	暗灰色	600mm	RAL 7021	是
10630-043	42U	2000mm	暗灰色	600mm	RAL 7021	否

Table 2/3						
物料号	覆层材料	深度	覆层颜色	包装数量	符合	完成
10630-044	钢	800mm	暗灰色	1	IEC 60529, IEC 61587-1, IEC 60297-3-100, IEC 61587-3	粉末涂层
10630-043	钢	800mm	暗灰色	1	IEC 60529, IEC 61587-1, IEC 60297-3-100, IEC 61587-3	粉末涂层

Table 3/3		
物料号	材料	快速发货
10630-044	钢	No
10630-043	钢	No

其他产品详情

ServicePlus EMC 上提供了更多尺寸和版本。请单独订购基座/底座。如装配托盘和滑轨，需要另外订购一对角轨。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



我们强大的品牌组合:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE