

Varistar CP 重型交叉构件



侧面支撑梁，用于支持 800 mm 宽机柜中的 19" 立柱，静态承载能力为 1600 kg。模数孔样式有助于按 25 mm 增量轻松安装 19" 立柱。



功能

侧面横梁，用于支持800 mm宽机柜中间 19" 立柱，静态承载能力为 1600 千克

模数孔结构有助于按 25 mm增量轻松安装 19" 立柱

技术参数

产品类型: 支架
材料: 钢
搭配: Varistar CP

Table 1/2

物料号	深度	包装数量	颜色	颜色代码	完成	包装单位
24630-008	1000mm	4	暗灰色	RAL 7021	粉末涂层	对
24630-091	900mm	4	暗灰色	RAL 7021	粉末涂层	对
24630-090	800mm	4	暗灰色	RAL 7021	粉末涂层	对
24630-089	600mm	4	暗灰色	RAL 7021	粉末涂层	对
24630-010	1200mm	4	暗灰色	RAL 7021	粉末涂层	对

物料号	深度	包装数量	颜色	颜色代码	完成	包装单位
24630-009	1100mm	4	暗灰色	RAL 7021	粉末涂层	对

Table 2/2	
物料号	快速发货
24630-008	No
24630-091	No
24630-090	No
24630-089	No
24630-010	No
24630-009	No

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书。或者向你的 nVent

North America	Europe	Asia	Middle East & India
All locations	Straubenhardt, Germany	Shanghai, China	Dubai, United Arab
+1.763.422.2661	+49.7082.794.0	+86.21.2412.6943	Emirates
Chat with us:	Betschdorf, France	Qingdao, China	+971.4.378.1700
nvent.com/schroff	+33.3.88.90.64.90	+86.532.8771.6101	Bangalore, India
	Warsaw, Poland	Singapore	+91.80.6715.2001
	+48.22.209.98.35	+65.6768.5800	Istanbul, Turkey
	Assago, Italy	Shin-Yokohama, Japan	+90.216.250.7374
	+39.02.932.7141	+81.45.476.0271	Chat with us:
	Chat with us:	Chat with us:	nvent.com/schroff
	nvent.com/schroff	nvent.com/schroff	



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE