

Varistar CP IP 55 机柜



Varistar: Highly versatile, robust welded steel frame electronics cabinet with a wide range of available features including protection against dust and water (IP20 and IP55), cooling options from fans to 40kW air-to-water chillers, shock, vibration and seismic resistance up to NEBS GR-63-CORE Bellcore zone 4 and industry leading radio-frequency/electromagnetic (RFI / EMI) shielding of 60 dB at 1 GHz, 40 dB at 3 GHz (tested to IEC 61587-3).

功能

防护类型 IP 55

带 3 点锁定门和螺钉固定侧面板

静态承载能力 1600 千克

侧面板和后面板可由一人安装

EN45545-2 防火安全垫片

技术参数

静态负载: 1600kg

产品类型: 机柜

防护等级: IP55

覆层颜色代码: RAL 7021

框架材料: 钢

Table 1/3

物料号	机架高度	高度	框架颜色	宽度	框架颜色代码	覆层材料
10630-042	42U	2000mm	暗灰色	600mm	RAL 7021	钢
10630-041	42U	2000mm	暗灰色	600mm	RAL 7021	钢

Table 2/3						
物料号	深度	覆层颜色	类型	包装数量	符合	完成
10630-042	600mm	暗灰色	钢制门，平板	1	IEC 60529, IEC 61587-1, IEC 60297-3-100	粉末涂层
10630-041	600mm	暗灰色	钢制玻璃门	1	IEC 60529, IEC 61587-1, IEC 60297-3-100	粉末涂层

Table 3/3		
物料号	材料	快速发货
10630-042	钢	No
10630-041	钢	No

其他产品详情

ServicePLUS IP 55 上提供更多尺寸和版本。请单独订购基座/底座。对于层板和滑轨装配，需要有额外一对面板/滑轨安装件。

警告

本文件仅供参考，不作为任何法律文件使用。如有更改，恕不另行通知。所有其他商标均为其各自所有者的财产。nVent 保留更改规格的权利，恕不另行通知。

North America	Europe	Asia	Middle East & India
All locations	Straubenhardt, Germany	Shanghai, China	Dubai, United Arab Emirates
+1.763.422.2661	+49.7082.794.0	+86.21.2412.6943	
Chat with us:	Betschdorf, France	Qingdao, China	+971.4.378.1700
nvent.com/schroff	+33.3.88.90.64.90	+86.532.8771.6101	Bangalore, India
	Warsaw, Poland	Singapore	+91.80.6715.2001
	+48.22.209.98.35	+65.6768.5800	Istanbul, Turkey
	Assago, Italy	Shin-Yokohama, Japan	+90.216.250.7374
	+39.02.932.7141	+81.45.476.0271	Chat with us:
	Chat with us:	Chat with us:	nvent.com/schroff
	nvent.com/schroff	nvent.com/schroff	



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE