

Varistar CP Rear Panel with Mounting Plate, 尺寸缩短型



尺寸缩短后面板，带安装板，现在作为独立的 SKU 提供，以更好地管理电缆。

功能

螺钉固定, 单人可安装的坚固侧板

连接板高度 400 mm

后面板的高度比机柜高度低 400 mm

内部镀锌

技术参数

产品类型: 机柜/机架面板

防护等级: IP55

材料: 不锈钢

Table 1/1

物料号	机架高度	高度	宽度	包装数量	完成	快速发货
21630-380	42U	2000mm	600mm	1	粉末涂层	No
21630-381	42U	2000mm	800mm	1	粉末涂层	No
21630-378	38U	1800mm	600mm	1	粉末涂层	No

物料号	机架高度	高度	宽度	包装数量	完成	快速发货
21630-383	47U	2200mm	800mm	1	粉末涂层	No
21630-379	38U	1800mm	800mm	1	粉末涂层	No
21630-382	47U	2200mm	600mm	1	粉末涂层	No

其他产品详情

请单独购买接地套件。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE