

Varistar CP 服务器机柜



符合高静态负载要求的焊接钢框架。适用于 IT 行业的 19" 集成机柜。

功能

预配置, 立即可用型机柜

静态承载重能力高达 1600 千克, 动态 1000 kg

防护等级 IP 20

可以安装不同的 IT 设备

实现自前向后冷却的集成式空气面板

可轻松集成到通道密封系统中

技术参数

静态负载: 1600kg

产品类型: 机架

覆层颜色代码: RAL 7021

框架材料: 钢

Table 1/2

物料号	机架高度	高度	覆层材料	宽度	覆层颜色	深度
-----	------	----	------	----	------	----

10630-018	42U	2000mm	钢	800mm	暗灰色	1200mm
10630-020	47U	2200mm	钢	800mm	暗灰色	1200mm
10630-017	42U	2000mm	钢	600mm	暗灰色	1200mm
10630-019	47U	2200mm	钢	600mm	暗灰色	1200mm
10630-023	42U	2000mm	钢	600mm	暗灰色	1200mm
10630-024	42U	2000mm	钢	800mm	暗灰色	1200mm
10630-025	47U	2200mm	钢	600mm	暗灰色	1200mm
10630-026	47U	2200mm	钢	800mm	暗灰色	1200mm

Table 2/2						
物料号	类型	包装数量	动态荷载	完成	材料	快速发货
10630-018	标准	1	1000kgf	粉末涂层	钢	No
10630-020	标准	1	1000kgf	粉末涂层	钢	No
10630-017	标准	1	1000kgf	粉末涂层	钢	No
10630-019	标准	1	1000kgf	粉末涂层	钢	No
10630-023	并排	1	1000kgf	粉末涂层	钢	No
10630-024	并排	1	1000kgf	粉末涂层	钢	No
10630-025	并排	1	1000kgf	粉末涂层	钢	No
10630-026	并排	1	1000kgf	粉末涂层	钢	No

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE