

Varistar CP 钢板门, Plain With 1-Point Locking



适用 IP 20 应用的 Varistar CP 钢板门，单点锁定。

功能

带 IP 20 防护等级单点锁的钢门

开门角度 180°

开门角度 180°

技术参数

产品类型: 机柜门

防护等级: IP20

材料: 钢

Table 1/2

物料号	机架高度	高度	宽度	锁定类型	包装数量	颜色
21630-493	24U	1200mm	600mm	单点锁定	1	暗灰色
21630-400	24U	1200mm	600mm	单点锁定	1	暗灰色
21630-494	24U	1200mm	800mm	单点锁定	1	暗灰色

物料号	机架高度	高度	宽度	锁定类型	包装数量	颜色
21630-401	24U	1200mm	800mm	单点锁定	1	暗灰色
21630-495	29U	1400mm	600mm	单点锁定	1	暗灰色
21630-402	29U	1400mm	600mm	单点锁定	1	暗灰色
21630-496	29U	1400mm	800mm	单点锁定	1	暗灰色
21630-403	29U	1400mm	800mm	单点锁定	1	暗灰色
21630-497	33U	1600mm	600mm	单点锁定	1	暗灰色
21630-404	33U	1600mm	600mm	单点锁定	1	暗灰色
21630-498	33U	1600mm	800mm	单点锁定	1	暗灰色
21630-405	33U	1600mm	800mm	单点锁定	1	暗灰色
21630-499	38U	1800mm	600mm	单点锁定	1	暗灰色
21630-406	38U	1800mm	600mm	单点锁定	1	暗灰色
21630-500	38U	1800mm	800mm	单点锁定	1	暗灰色
21630-407	38U	1800mm	800mm	单点锁定	1	暗灰色
21630-501	42U	2000mm	600mm	单点锁定	1	暗灰色
21630-002	42U	2000mm	600mm	单点锁定	1	暗灰色
21630-502	42U	2000mm	800mm	单点锁定	1	暗灰色
21630-009	42U	2000mm	800mm	单点锁定	1	暗灰色

物料号	机架高度	高度	宽度	锁定类型	包装数量	颜色
21630-503	47U	2200mm	600mm	单点锁定	1	暗灰色
21630-003	47U	2200mm	600mm	单点锁定	1	暗灰色
21630-504	47U	2200mm	800mm	单点锁定	1	暗灰色
21630-010	47U	2200mm	800mm	单点锁定	1	暗灰色
21630-004	52U	2450mm	600mm	单点锁定	1	暗灰色
21630-011	52U	2450mm	800mm	单点锁定	1	暗灰色

Table 2/2						
物料号	颜色代码	符合	完成	类型	搭配	快速发货
21630-493	RAL 7021	IEC 61587-1	粉末涂层	钢板门	Varistar CP	No
21630-400	RAL 7021	IEC 61587-1, IEC 61587-3	粉末涂层	钢板门	Varistar CP	No
21630-494	RAL 7021	IEC 61587-1	粉末涂层	钢板门	Varistar CP	No
21630-401	RAL 7021	IEC 61587-1, IEC 61587-3	粉末涂层	钢板门	Varistar CP	No
21630-495	RAL 7021	IEC 61587-1	粉末涂层	钢板门	Varistar CP	No
21630-402	RAL 7021	IEC 61587-1, IEC 61587-3	粉末涂层	钢板门	Varistar CP	No
21630-496	RAL 7021	IEC 61587-1	粉末涂层	钢板门	Varistar CP	No
21630-403	RAL 7021	IEC 61587-1, IEC 61587-3	粉末涂层	钢板门	Varistar CP	No
21630-497	RAL 7021	IEC 61587-1	粉末涂层	钢板门	Varistar CP	No

物料号	颜色代码	符合	完成	类型	搭配	快速发货
21630-404	RAL 7021	IEC 61587-1, IEC 61587-3	粉末涂层	钢板门	Varistar CP	No
21630-498	RAL 7021	IEC 61587-1	粉末涂层	钢板门	Varistar CP	No
21630-405	RAL 7021	IEC 61587-1, IEC 61587-3	粉末涂层	钢板门	Varistar CP	No
21630-499	RAL 7021	IEC 61587-1	粉末涂层	钢板门	Varistar CP	No
21630-406	RAL 7021	IEC 61587-1, IEC 61587-3	粉末涂层	钢板门	Varistar CP	No
21630-500	RAL 7021	IEC 61587-1	粉末涂层	钢板门	Varistar CP	No
21630-407	RAL 7021	IEC 61587-1, IEC 61587-3	粉末涂层	钢板门	Varistar CP	No
21630-501	RAL 7021	IEC 61587-1	粉末涂层	钢板门	Varistar CP	No
21630-002	RAL 7021	IEC 61587-1, IEC 61587-3	粉末涂层	钢板门	Varistar CP	No
21630-502	RAL 7021	IEC 61587-1	粉末涂层	钢板门	Varistar CP	No
21630-009	RAL 7021	IEC 61587-1, IEC 61587-3	粉末涂层	钢板门	Varistar CP	No
21630-503	RAL 7021	IEC 61587-1	粉末涂层	钢板门	Varistar CP	No
21630-003	RAL 7021	IEC 61587-1, IEC 61587-3	粉末涂层	钢板门	Varistar CP	No
21630-504	RAL 7021	IEC 61587-1	粉末涂层	钢板门	Varistar CP	No
21630-010	RAL 7021	IEC 61587-1, IEC 61587-3	粉末涂层	钢板门	Varistar CP	No
21630-004	RAL 7021	IEC 61587-1, IEC 61587-3	粉末涂层	钢板门	Varistar CP	No
21630-011	RAL 7021	IEC 61587-1, IEC 61587-3	粉末涂层	钢板门	Varistar CP	No

其他产品详情

24U - 33U IP20 门配有 2 个铰链，38U - 52U IP20 门配有 3 个铰链，以确保较高机柜的坚固 IP20 关闭结构

如需更换 1333 DIN 锁杠杆式把手，请单独订购杠杆式把手 24630003 和 DIN 锁

请单独购买接地套件。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE