

Varistar 服务器机柜, RAL 9003, 并排



符合高静态承载要求的服务器机架，已完全装配和接地，包括白色粉末涂层的并排套件。

认证



功能

静态承载能力高达 1600 千克

防护等级 IP 20

可安装不同的服务器

带网门的服务器机柜, 通风率 78%

RAL 9003 (白色)

技术参数

Table 1/3

物料号	类型	框架材料	覆层材料	框架颜色	框架颜色代码	覆层颜色
12130-275	并排	钢	钢	信号白	RAL 9003	信号白
12130-276	并排	钢	钢	信号白	RAL 9003	信号白

物料号	类型	框架材料	覆层材料	框架颜色	框架颜色代码	覆层颜色
12130-285	并排	钢	钢	信号白	RAL 9003	信号白
12130-286	并排	钢	钢	信号白	RAL 9003	信号白
12130-279	并排	钢	钢	信号白	RAL 9003	信号白
12130-280	并排	钢	钢	信号白	RAL 9003	信号白
12130-289	并排	钢	钢	信号白	RAL 9003	信号白
12130-290	并排	钢	钢	信号白	RAL 9003	信号白
12130-283	并排	钢	钢	信号白	RAL 9003	信号白
12130-284	并排	钢	钢	信号白	RAL 9003	信号白
12130-293	并排	钢	钢	信号白	RAL 9003	信号白
12130-294	并排	钢	钢	信号白	RAL 9003	信号白

Table 2/3						
物料号	覆层颜色代码	机架高度	高度	宽度	深度	静态负载
12130-275	RAL 9003	42U	2000mm	600mm	1000mm	1600kg
12130-276	RAL 9003	42U	2000mm	800mm	1000mm	1600kg
12130-285	RAL 9003	42U	2000mm	600mm	1200mm	1600kg
12130-286	RAL 9003	42U	2000mm	800mm	1200mm	1600kg
12130-279	RAL 9003	47U	2200mm	600mm	1000mm	1600kg

物料号	覆层颜色代码	机架高度	高度	宽度	深度	静态负载
12130-280	RAL 9003	47U	2200mm	800mm	1000mm	1600kg
12130-289	RAL 9003	47U	2200mm	600mm	1200mm	1600kg
12130-290	RAL 9003	47U	2200mm	800mm	1200mm	1600kg
12130-283	RAL 9003	52U	2450mm	600mm	1000mm	1600kg
12130-284	RAL 9003	52U	2450mm	800mm	1000mm	1600kg
12130-293	RAL 9003	52U	2450mm	600mm	1200mm	1600kg
12130-294	RAL 9003	52U	2450mm	800mm	1200mm	1600kg

Table 3/3	
物料号	快速发货
12130-275	No
12130-276	No
12130-285	No
12130-286	No
12130-279	No
12130-280	No
12130-289	No
12130-290	No

物料号	快速发货
12130-283	No
12130-284	No
12130-293	No
12130-294	No

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE