


Vertical rear busbar supports | Strømfordeling, MSFH



This fix system vertical busbar support, MSFH, for two bars up to 40 x 10 mm, is available off the shelf and has been tested according to IEC 61439.

FUNKTIONER

Beskrivelse: Busbar supports up to 1600A to be mounted vertically behind the fixed compartments. Mounts to the vertical profiles MSFP. Rated short-time withstand current up to 35 kA with rear supports and up to 50 kA with rear and front supports.

Materiale: Polycarbonate reinforced with 10% of glass material.

Levering inkluderer: 7 busbar supports for 3 phases and neutral, and mounting material.

A flexible and reliable solution that ensures procurement, design and installation can be done efficiently reducing the labour time required

Fix system vertical profiles (MSFP) are required in order to mount the busbar supports

Busbar supports up to 1600A to be mounted vertically behind the fixed compartments

Mounts to the vertical profiles MSFP

Rated short-time withstand current up to 35 kA with rear supports and up to 50 kA with rear and front supports

Delivery: 7 busbar supports for 3 phases and neutral, and mounting material

SPECIFIKATIONER

Table 1/1

Katalognummer	Højde	Bredde	Dybde	Enclosure Material	Produktfamilie	Materiale
MSFH06	40mm	600mm	45mm	Lakeret Stål	Free-Standing	Polycarbonate

YDERLIGERE PRODUKTOPLYSNINGER

*In: Rated current. *Icw: Rated short-time withstand current.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE