


# Frame Type Plug-In Unit Side Panel Corner Profile, PCB Depth 160 mm

## CATALOG NUMBER

**34812-102**



Side Panel corner profile for frame type plug-in unit, PCB depth 160 and 220 mm.

## CERTIFICATIONS



## FEATURES

Corner profile (top and bottom)

Integrated lateral groove in corner profile to accept a PCB

Side Panel of plug-in unit is constructed with two components

Plate is inserted between two corner profiles

## PRODUCT ATTRIBUTES

Package Quantity: 1

Depth (D): 167mm

Finish: Passivated


Length (L): 160mm

Product Type: Corner Profile

Net Weight: 0.043kg

Please order side plate separately.

## DIAGRAMS



nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

Straubenhardt, Germany  
 +49.7082.794.0  
 Betschdorf, France  
 +33.3.88.90.64.90  
 Warsaw, Poland  
 +48.22.209.98.35  
 Assago, Italy  
 +39.02.932.7141  
 Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE