

# Joint Bond T7 Complete Welder Pair, Signal, 1" Tab Bond Terminal Style, 5/16" Bondstrand

## Data Solutions

### CATALOG NUMBER

**SBTBT7B**



### FEATURES

Complete welder assembly provides a convenient means of attaching jumper bonds to the head of the rail, across the joint

Connection is made within the confines of the splice bar

Includes mold cleaner and flint ignitor

### PRODUCT ATTRIBUTES

Material: Steel; Graphite

Rail Type: 85 lb to 141 lb T-Rail Sections

Bond Terminal Style: 1" Tab

Conductor Size: 5/16" Bondstrand

Conductor Outer Diameter, Nominal: 7.94mm

Welder Style: T7

Mold Only: No

Replacement Mold: SBS898

Welding Material: SB32 x 2, Sold Separately

Bond Clip: SBS119 x 2, Sold Separately

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**