


RatiopacPRO 19" Case, Retrofittable Shielding With Handles



The nVent SCHROFF RatiopacPRO case provides electronics protection for 19" and individual electronic assemblies. This flexible and robust case is simple to convert from desktop to a 19" rack mount case and includes four different style options. This version of the case provides front handles for easier handling of the case.

CERTIFICATIONS



FEATURES

Cases for individual assembly with 19" standard components or specific internal mounting, e.g. with mounting plate

Designed for insertion/extractor handles in accordance with IEC 60297-3-102 and IEEE 1101.10 for CompactPCI and VME64x applications

Version with front handles

Retrofittable EMC shielding

For board depth 160 mm, 220 mm, 280 mm, and 340 mm (depending on case depth)

Symmetrical design, identical front and rear side

No visible screws; cladding parts removable without tools

Conforms with DIN EN 62368-1

SPECIFICATIONS

Product Type: Case

Product Family: RatiopacPRO

Table 1/3

Catalog Number	Rack Height	Rack Width	Depth	Package Quantity	Usable Height	Usable Width
24571-839	6U	84HP	435.5mm	1	245.7mm	432mm
24571-840	6U	84HP	495.5mm	1	245.7mm	432mm
24572-213	5U	28HP	255.5mm	1	201.25mm	148mm
24572-216	5U	28HP	315.5mm	1	201.25mm	148mm
24572-225	5U	42HP	255.5mm	1	201.25mm	219mm
24572-228	5U	42HP	315.5mm	1	201.25mm	219mm
24572-229	5U	42HP	375.5mm	1	201.25mm	219mm
24572-237	5U	63HP	255.5mm	1	201.25mm	326mm
24572-240	5U	63HP	315.5mm	1	201.25mm	326mm
24572-241	5U	63HP	375.5mm	1	201.25mm	326mm
24572-249	5U	84HP	255.5mm	1	201.25mm	432mm
24572-252	5U	84HP	315.5mm	1	201.25mm	432mm
24572-253	5U	84HP	375.5mm	1	201.25mm	432mm
24572-254	5U	84HP	435.5mm	1	201.25mm	432mm
24572-255	5U	84HP	495.5mm	1	201.25mm	432mm
24572-357	5U	28HP	255.5mm	1	201.25mm	148mm
24572-360	5U	28HP	315.5mm	1	201.25mm	148mm
24572-369	5U	42HP	255.5mm	1	201.25mm	219mm

CatalogNumber	Rack Height	Rack Width	Depth	Package Quantity	Usable Height	Usable Width
24572-372	5U	42HP	315.5mm	1	201.25mm	219mm
24572-373	5U	42HP	375.5mm	1	201.25mm	219mm
24572-381	5U	63HP	255.5mm	1	201.25mm	326mm
24572-384	5U	63HP	315.5mm	1	201.25mm	326mm
24572-385	5U	63HP	375.5mm	1	201.25mm	326mm
24572-393	5U	84HP	255.5mm	1	201.25mm	432mm
24572-396	5U	84HP	315.5mm	1	201.25mm	432mm
24572-397	5U	84HP	375.5mm	1	201.25mm	432mm
24572-398	5U	84HP	435.5mm	1	201.25mm	432mm
24572-399	5U	84HP	495.5mm	1	201.25mm	432mm
24572-720	2U	42HP	248.74mm	1	88.1mm	213.94mm
24572-723	2U	42HP	248.74mm	1	88.1mm	213.94mm
24572-730	2U	63HP	355.42mm	1	88.1mm	320.62mm
24572-733	2U	63HP	35.42mm	1	88.1mm	32.62mm
24571-702	3U	28HP	255.5mm	1	112.3mm	148mm
24571-705	3U	28HP	315.5mm	1	112.3mm	148mm
24571-714	3U	42HP	255.5mm	1	112.3mm	219mm
24571-717	3U	42HP	315.5mm	1	112.3mm	219mm

CatalogNumber	Rack Height	Rack Width	Depth	Package Quantity	Usable Height	Usable Width
24571-718	3U	42HP	375.5mm	1	112.3mm	219mm
24571-726	3U	63HP	255.5mm	1	112.3mm	326mm
24571-729	3U	63HP	315.5mm	1	112.3mm	326mm
24571-730	3U	63HP	375.5mm	1	112.3mm	326mm
24571-738	3U	84HP	255.5mm	1	112.3mm	432mm
24571-741	3U	84HP	315.5mm	1	112.3mm	432mm
24571-742	3U	84HP	375.5mm	1	112.3mm	432mm
24571-743	3U	84HP	435.5mm	1	112.3mm	432mm
24571-744	3U	84HP	495.5mm	1	112.3mm	432mm
24571-750	4U	28HP	255.5mm	1	156.8mm	148mm
24571-753	4U	28HP	315.5mm	1	156.8mm	148mm
24571-762	4U	42HP	255.5mm	1	156.8mm	219mm
24571-765	4U	42HP	315.5mm	1	156.8mm	219mm
24571-766	4U	42HP	375.5mm	1	156.8mm	219mm
24571-774	4U	63HP	255.5mm	1	156.8mm	326mm
24571-777	4U	63HP	315.5mm	1	156.8mm	326mm
24571-778	4U	63HP	375.5mm	1	156.8mm	326mm
24571-786	4U	84HP	255.5mm	1	156.8mm	432mm

CatalogNumber	Rack Height	Rack Width	Depth	Package Quantity	Usable Height	Usable Width
24571-789	4U	84HP	315.5mm	1	156.8mm	432mm
24571-790	4U	84HP	375.5mm	1	156.8mm	432mm
24571-791	4U	84HP	435.5mm	1	156.8mm	432mm
24571-792	4U	84HP	495.5mm	1	156.8mm	432mm
24571-798	6U	28HP	255.5mm	1	245.7mm	148mm
24571-801	6U	28HP	315.5mm	1	245.7mm	148mm
24571-810	6U	42HP	255.5mm	1	245.7mm	219mm
24571-813	6U	42HP	315.5mm	1	245.7mm	219mm
24571-814	6U	42HP	375.5mm	1	245.7mm	219mm
24571-822	6U	63HP	255.5mm	1	245.7mm	326mm
24571-825	6U	63HP	315.5mm	1	245.7mm	326mm
24571-826	6U	63HP	375.5mm	1	245.7mm	326mm
24571-834	6U	84HP	255.5mm	1	245.7mm	432mm
24571-837	6U	84HP	315.5mm	1	245.7mm	432mm
24571-838	6U	84HP	375.5mm	1	245.7mm	432mm

Table 2/3

Catalog Number	Front Frame Construction	Cooling Option	Complies With	EMC Shielding	Finish	Height
----------------	--------------------------	----------------	---------------	---------------	--------	--------

24571-839	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	265.9mm
24571-840	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	265.9mm
24572-213	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	221.5mm
24572-216	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	221.5mm
24572-225	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	221.5mm
24572-228	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	221.5mm
24572-229	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	221.5mm
24572-237	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	221.5mm

24572-240	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	221.5mm
24572-241	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	221.5mm
24572-249	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	221.5mm
24572-252	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	221.5mm
24572-253	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	221.5mm
24572-254	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	221.5mm
24572-255	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	221.5mm
24572-357	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	221.5mm

24572-360	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	221.5mm
24572-369	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	221.5mm
24572-372	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	221.5mm
24572-373	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	221.5mm
24572-381	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	221.5mm
24572-384	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	221.5mm
24572-385	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	221.5mm
24572-393	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	221.5mm

24572-396	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	221.5mm
24572-397	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	221.5mm
24572-398	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	221.5mm
24572-399	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	221.5mm
24572-720	Side Trim, Horizontal Rails	Yes	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Yes	Passivated, Powder Coated	88.1mm
24572-723	Side Trim, Horizontal Rails	Yes	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Yes	Passivated, Powder Coated	88.1mm
24572-730	Side Trim, Horizontal Rails	Yes	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Yes	Passivated, Powder Coated	88.1mm
24572-733	Side Trim, Horizontal Rails	Yes	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Yes	Passivated, Powder Coated	88.1mm

24571-702	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	132.6mm
24571-705	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	132.6mm
24571-714	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	132.6mm
24571-717	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	132.6mm
24571-718	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	132.6mm
24571-726	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	132.6mm
24571-729	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	132.6mm
24571-730	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	132.6mm

24571-738	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	132.6mm
24571-741	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	132.6mm
24571-742	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	132.6mm
24571-743	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	132.6mm
24571-744	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	132.6mm
24571-750	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	177mm
24571-753	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	177mm
24571-762	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	177mm

24571-765	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	177mm
24571-766	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	177mm
24571-774	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	177mm
24571-777	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	177mm
24571-778	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	177mm
24571-786	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	177mm
24571-789	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	177mm
24571-790	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	177mm

24571-791	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	177mm
24571-792	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	177mm
24571-798	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	265.9mm
24571-801	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	265.9mm
24571-810	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	265.9mm
24571-813	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	265.9mm
24571-814	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	265.9mm
24571-822	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	265.9mm

24571-825	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	265.9mm
24571-826	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	265.9mm
24571-834	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	265.9mm
24571-837	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	265.9mm
24571-838	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Powder Coated	265.9mm

Table 3/3

Catalog Number	Material	Protection Rating	Static Load	Type	Width	Quick Ship
24571-839	Aluminum	IP20	25kg	Case for Individual Electronic Components	448.9mm	No
24571-840	Aluminum	IP20	25kg	Case for Individual Electronic Components	448.9mm	No
24572-213	Aluminum	IP20	25kg	Case for Individual Electronic Components	164.4mm	No

CatalogNumber	Material	Protection Rating	Static Load	Type	Width	Quick Ship
24572-216	Aluminum	IP20	25kg	Case for Individual Electronic Components	164.4mm	No
24572-225	Aluminum	IP20	25kg	Case for Individual Electronic Components	235.5mm	No
24572-228	Aluminum	IP20	25kg	Case for Individual Electronic Components	235.5mm	No
24572-229	Aluminum	IP20	25kg	Case for Individual Electronic Components	235.5mm	No
24572-237	Aluminum	IP20	25kg	Case for Individual Electronic Components	342.4mm	No
24572-240	Aluminum	IP20	25kg	Case for Individual Electronic Components	342.4mm	No
24572-241	Aluminum	IP20	25kg	Case for Individual Electronic Components	342.4mm	No
24572-249	Aluminum	IP20	25kg	Case for Individual Electronic Components	448.9mm	No
24572-252	Aluminum	IP20	25kg	Case for Individual Electronic Components	448.9mm	No
24572-253	Aluminum	IP20	25kg	Case for Individual Electronic Components	448.9mm	No
24572-254	Aluminum	IP20	25kg	Case for Individual Electronic Components	448.9mm	No

CatalogNumber	Material	Protection Rating	Static Load	Type	Width	Quick Ship
24572-255	Aluminum	IP20	25kg	Case for Individual Electronic Components	448.9mm	No
24572-357	Aluminum	IP20	25kg	Case for Individual Electronic Components	164.4mm	No
24572-360	Aluminum	IP20	25kg	Case for Individual Electronic Components	164.4mm	No
24572-369	Aluminum	IP20	25kg	Case for Individual Electronic Components	235.5mm	No
24572-372	Aluminum	IP20	25kg	Case for Individual Electronic Components	235.5mm	No
24572-373	Aluminum	IP20	25kg	Case for Individual Electronic Components	235.5mm	No
24572-381	Aluminum	IP20	25kg	Case for Individual Electronic Components	342.4mm	No
24572-384	Aluminum	IP20	25kg	Case for Individual Electronic Components	342.4mm	No
24572-385	Aluminum	IP20	25kg	Case for Individual Electronic Components	342.4mm	No
24572-393	Aluminum	IP20	25kg	Case for Individual Electronic Components	448.9mm	No
24572-396	Aluminum	IP20	25kg	Case for Individual Electronic Components	448.9mm	No

CatalogNumber	Material	Protection Rating	Static Load	Type	Width	Quick Ship
24572-397	Aluminum	IP20	25kg	Case for Individual Electronic Components	448.9mm	No
24572-398	Aluminum	IP20	25kg	Case for Individual Electronic Components	448.9mm	No
24572-399	Aluminum	IP20	25kg	Case for Individual Electronic Components	448.9mm	No
24572-720	Aluminum	IP20		Case for 19" Components	235.5mm	No
24572-723	Aluminum	IP20		Case for 19" Components	235.5mm	No
24572-730	Aluminum	IP20		Case for 19" Components	342.4mm	No
24572-733	Aluminum	IP20		Case for 19" Components	342.4mm	No
24571-702	Aluminum	IP20	25kg	Case for Individual Electronic Components	164.4mm	No
24571-705	Aluminum	IP20	25kg	Case for Individual Electronic Components	164.4mm	No
24571-714	Aluminum	IP20	25kg	Case for Individual Electronic Components	235.5mm	No
24571-717	Aluminum	IP20	25kg	Case for Individual Electronic Components	235.5mm	No
24571-718	Aluminum	IP20	25kg	Case for Individual Electronic Components	235.5mm	No

CatalogNumber	Material	Protection Rating	Static Load	Type	Width	Quick Ship
24571-726	Aluminum	IP20	25kg	Case for Individual Electronic Components	342.4mm	No
24571-729	Aluminum	IP20	25kg	Case for Individual Electronic Components	342.4mm	No
24571-730	Aluminum	IP20	25kg	Case for Individual Electronic Components	342.4mm	No
24571-738	Aluminum	IP20	25kg	Case for Individual Electronic Components	448.9mm	No
24571-741	Aluminum	IP20	25kg	Case for Individual Electronic Components	448.9mm	No
24571-742	Aluminum	IP20	25kg	Case for Individual Electronic Components	448.9mm	No
24571-743	Aluminum	IP20	25kg	Case for Individual Electronic Components	448.9mm	No
24571-744	Aluminum	IP20	25kg	Case for Individual Electronic Components	448.9mm	No
24571-750	Aluminum	IP20	25kg	Case for Individual Electronic Components	164.4mm	No
24571-753	Aluminum	IP20	25kg	Case for Individual Electronic Components	164.4mm	No
24571-762	Aluminum	IP20	25kg	Case for Individual Electronic Components	235.5mm	No

CatalogNumber	Material	Protection Rating	Static Load	Type	Width	Quick Ship
24571-765	Aluminum	IP20	25kg	Case for Individual Electronic Components	235.5mm	No
24571-766	Aluminum	IP20	25kg	Case for Individual Electronic Components	235.5mm	No
24571-774	Aluminum	IP20	25kg	Case for Individual Electronic Components	342.4mm	No
24571-777	Aluminum	IP20	25kg	Case for Individual Electronic Components	342.4mm	No
24571-778	Aluminum	IP20	25kg	Case for Individual Electronic Components	342.4mm	No
24571-786	Aluminum	IP20	25kg	Case for Individual Electronic Components	448.9mm	No
24571-789	Aluminum	IP20	25kg	Case for Individual Electronic Components	448.9mm	No
24571-790	Aluminum	IP20	25kg	Case for Individual Electronic Components	448.9mm	No
24571-791	Aluminum	IP20	25kg	Case for Individual Electronic Components	448.9mm	No
24571-792	Aluminum	IP20	25kg	Case for Individual Electronic Components	448.9mm	No
24571-798	Aluminum	IP20	25kg	Case for Individual Electronic Components	164.4mm	No

CatalogNumber	Material	Protection Rating	Static Load	Type	Width	Quick Ship
24571-801	Aluminum	IP20	25kg	Case for Individual Electronic Components	164.4mm	No
24571-810	Aluminum	IP20	25kg	Case for Individual Electronic Components	235.5mm	No
24571-813	Aluminum	IP20	25kg	Case for Individual Electronic Components	235.5mm	No
24571-814	Aluminum	IP20	25kg	Case for Individual Electronic Components	235.5mm	No
24571-822	Aluminum	IP20	25kg	Case for Individual Electronic Components	342.4mm	No
24571-825	Aluminum	IP20	25kg	Case for Individual Electronic Components	342.4mm	No
24571-826	Aluminum	IP20	25kg	Case for Individual Electronic Components	342.4mm	No
24571-834	Aluminum	IP20	25kg	Case for Individual Electronic Components	448.9mm	No
24571-837	Aluminum	IP20	25kg	Case for Individual Electronic Components	448.9mm	No
24571-838	Aluminum	IP20	25kg	Case for Individual Electronic Components	448.9mm	No

ADDITIONAL PRODUCT DETAILS

Modifications (special colours or sizes).

Custom solutions (cut-outs in top cover, base plate or side panels).

Assembly service from 1 piece.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE