

Outdoor Modular Cabinet Triple Doors

Data Solutions



Telecom and Railway applications require sophisticated electronics in outdoor setups. nVent SCHROFF Outdoor cabinets shield such electronic components from extreme weather and vandalism, ensuring operational continuity. Modular construction allows multiple configurations in size and function along with multiple cooling options.

FEATURES

Aluminium profile frame with removable, double-walled cladding

IP 55 or NEMA 12~

Double-walled

Extensive range of 19" cabinet accessories

Access to cabinet from front, all sides possible upon request

100 mm high plinth, 200 and 300 mm possible

Top cover with louvers, can be upgraded with fans or A/C unit

RAL 7035 powder coating, other colors available upon request

SPECIFICATIONS

Frame Material: Aluminum

Table 1/3

Catalog Number	Product Type	Product Family	Rack Height	Height	Width	Depth
10149-874	Outdoor Cabinet	Modular	42U	2130mm	1900mm	1100mm
10149-875	Outdoor Cabinet	Modular	42U	2130mm	2100mm	1100mm

CatalogNumber	Product Type	Product Family	Rack Height	Height	Width	Depth
10149-882	Outdoor Cabinet	Modular	42U	2130mm	1900mm	1200mm
10149-883	Outdoor Cabinet	Modular	42U	2130mm	2100mm	1200mm
10149-506	Outdoor Cabinet	Modular	20U	1130mm	1900mm	500mm
10149-507	Outdoor Cabinet	Modular	20U	1130mm	2100mm	500mm
10149-514	Outdoor Cabinet	Modular	20U	1130mm	1900mm	600mm
10149-515	Outdoor Cabinet	Modular	20U	1130mm	2100mm	600mm
10149-522	Outdoor Cabinet	Modular	20U	1130mm	1900mm	700mm
10149-523	Outdoor Cabinet	Modular	20U	1130mm	2100mm	700mm
10149-530	Outdoor Cabinet	Modular	20U	1130mm	1900mm	800mm
10149-531	Outdoor Cabinet	Modular	20U	1130mm	2100mm	800mm
10149-538	Outdoor Cabinet	Modular	20U	1130mm	1900mm	900mm
10149-539	Outdoor Cabinet	Modular	20U	1130mm	2100mm	900mm
10149-546	Outdoor Cabinet	Modular	20U	1130mm	1900mm	1000mm
10149-547	Outdoor Cabinet	Modular	20U	1130mm	2100mm	1000mm
10149-554	Outdoor Cabinet	Modular	20U	1130mm	1900mm	1100mm
10149-555	Outdoor Cabinet	Modular	20U	1130mm	2100mm	1100mm
10149-562	Outdoor Cabinet	Modular	20U	1130mm	1900mm	1200mm
10149-563	Outdoor Cabinet	Modular	20U	1130mm	2100mm	1200mm

CatalogNumber	Product Type	Product Family	Rack Height	Height	Width	Depth
10149-570	Outdoor Cabinet	Modular	24U	1330mm	1900mm	500mm
10149-571	Outdoor Cabinet	Modular	24U	1330mm	2100mm	500mm
10149-578	Outdoor Cabinet	Modular	24U	1330mm	1900mm	600mm
10149-579	Outdoor Cabinet	Modular	24U	1330mm	2100mm	600mm
10149-586	Outdoor Cabinet	Modular	24U	1330mm	1900mm	700mm
10149-587	Outdoor Cabinet	Modular	24U	1330mm	2100mm	700mm
10149-594	Outdoor Cabinet	Modular	24U	1330mm	1900mm	800mm
10149-595	Outdoor Cabinet	Modular	24U	1330mm	2100mm	800mm
10149-602	Outdoor Cabinet	Modular	24U	1330mm	1900mm	900mm
10149-603	Outdoor Cabinet	Modular	24U	1330mm	2100mm	900mm
10149-610	Outdoor Cabinet	Modular	24U	1330mm	1900mm	1000mm
10149-611	Outdoor Cabinet	Modular	24U	1330mm	2100mm	1000mm
10149-618	Outdoor Cabinet	Modular	24U	1330mm	1900mm	1100mm
10149-619	Outdoor Cabinet	Modular	24U	1330mm	2100mm	1100mm
10149-626	Outdoor Cabinet	Modular	24U	1330mm	1900mm	1200mm
10149-627	Outdoor Cabinet	Modular	24U	1330mm	2100mm	1200mm
10149-634	Outdoor Cabinet	Modular	29U	1530mm	1900mm	500mm
10149-635	Outdoor Cabinet	Modular	29U	1530mm	2100mm	500mm

CatalogNumber	Product Type	Product Family	Rack Height	Height	Width	Depth
10149-642	Outdoor Cabinet	Modular	29U	1530mm	1900mm	600mm
10149-643	Outdoor Cabinet	Modular	29U	1530mm	2100mm	600mm
10149-650	Outdoor Cabinet	Modular	29U	1530mm	1900mm	700mm
10149-651	Outdoor Cabinet	Modular	29U	1530mm	2100mm	700mm
10149-658	Outdoor Cabinet	Modular	29U	1530mm	1900mm	800mm
10149-659	Outdoor Cabinet	Modular	29U	1530mm	2100mm	800mm
10149-666	Outdoor Cabinet	Modular	29U	1530mm	1900mm	900mm
10149-667	Outdoor Cabinet	Modular	29U	1530mm	2100mm	900mm
10149-674	Outdoor Cabinet	Modular	29U	1530mm	1900mm	1000mm
10149-675	Outdoor Cabinet	Modular	29U	1530mm	2100mm	1000mm
10149-682	Outdoor Cabinet	Modular	29U	1530mm	1900mm	1100mm
10149-683	Outdoor Cabinet	Modular	29U	1530mm	2100mm	1100mm
10149-690	Outdoor Cabinet	Modular	29U	1530mm	1900mm	1200mm
10149-691	Outdoor Cabinet	Modular	29U	1530mm	2100mm	1200mm
10149-698	Outdoor Cabinet	Modular	33U	1730mm	1900mm	500mm
10149-699	Outdoor Cabinet	Modular	33U	1730mm	2100mm	500mm
10149-706	Outdoor Cabinet	Modular	33U	1730mm	1900mm	600mm
10149-707	Outdoor Cabinet	Modular	33U	1730mm	2100mm	600mm

CatalogNumber	Product Type	Product Family	Rack Height	Height	Width	Depth
10149-714	Outdoor Cabinet	Modular	33U	1730mm	1900mm	700mm
10149-715	Outdoor Cabinet	Modular	33U	1730mm	2100mm	700mm
10149-722	Outdoor Cabinet	Modular	33U	1730mm	1900mm	800mm
10149-723	Outdoor Cabinet	Modular	33U	1730mm	2100mm	800mm
10149-730	Outdoor Cabinet	Modular	33U	1730mm	1900mm	900mm
10149-731	Outdoor Cabinet	Modular	33U	1730mm	2100mm	900mm
10149-738	Outdoor Cabinet	Modular	33U	1730mm	1900mm	1000mm
10149-739	Outdoor Cabinet	Modular	33U	1730mm	2100mm	1000mm
10149-746	Outdoor Cabinet	Modular	33U	1730mm	1900mm	1100mm
10149-747	Outdoor Cabinet	Modular	33U	1730mm	2100mm	1100mm
10149-754	Outdoor Cabinet	Modular	33U	1730mm	1900mm	1200mm
10149-755	Outdoor Cabinet	Modular	33U	1730mm	2100mm	1200mm
10149-762	Outdoor Cabinet	Modular	38U	1930mm	1900mm	500mm
10149-763	Outdoor Cabinet	Modular	38U	1930mm	2100mm	500mm
10149-770	Outdoor Cabinet	Modular	38U	1930mm	1900mm	600mm
10149-771	Outdoor Cabinet	Modular	38U	1930mm	2100mm	600mm
10149-778	Outdoor Cabinet	Modular	38U	1930mm	1900mm	700mm
10149-779	Outdoor Cabinet	Modular	38U	1930mm	2100mm	700mm

CatalogNumber	Product Type	Product Family	Rack Height	Height	Width	Depth
10149-786	Outdoor Cabinet	Modular	38U	1930mm	1900mm	800mm
10149-787	Outdoor Cabinet	Modular	38U	1930mm	2100mm	800mm
10149-794	Outdoor Cabinet	Modular	38U	1930mm	1900mm	900mm
10149-795	Outdoor Cabinet	Modular	38U	1930mm	2100mm	900mm
10149-802	Outdoor Cabinet	Modular	38U	1930mm	1900mm	1000mm
10149-803	Outdoor Cabinet	Modular	38U	1930mm	2100mm	1000mm
10149-810	Outdoor Cabinet	Modular	38U	1930mm	1900mm	1100mm
10149-811	Outdoor Cabinet	Modular	38U	1930mm	2100mm	1100mm
10149-818	Outdoor Cabinet	Modular	38U	1930mm	1900mm	1200mm
10149-819	Outdoor Cabinet	Modular	38U	1930mm	2100mm	1200mm
10149-826	Outdoor Cabinet	Modular	42U	2130mm	1900mm	500mm
10149-827	Outdoor Cabinet	Modular	42U	2130mm	2100mm	500mm
10149-834	Outdoor Cabinet	Modular	42U	2130mm	1900mm	600mm
10149-835	Outdoor Cabinet	Modular	42U	2130mm	2100mm	600mm
10149-842	Outdoor Cabinet	Modular	42U	2130mm	1900mm	700mm
10149-843	Outdoor Cabinet	Modular	42U	2130mm	2100mm	700mm
10149-850	Outdoor Cabinet	Modular	42U	2130mm	1900mm	800mm
10149-851	Outdoor Cabinet	Modular	42U	2130mm	2100mm	800mm

CatalogNumber	Product Type	Product Family	Rack Height	Height	Width	Depth
10149-858	Outdoor Cabinet	Modular	42U	2130mm	1900mm	900mm
10149-859	Outdoor Cabinet	Modular	42U	2130mm	2100mm	900mm
10149-866	Outdoor Cabinet	Modular	42U	2130mm	1900mm	1000mm
10149-867	Outdoor Cabinet	Modular	42U	2130mm	2100mm	1000mm

Table 2/3						
Catalog Number	Wall Type	Door Type	Burglar Resistance	Cooling	EMC Shielding	Battery Compartment
10149-874	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-875	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-882	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-883	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-506	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-507	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-514	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-515	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-522	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-523	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-530	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-531	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-538	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional

CatalogNumber	Wall Type	Door Type	Burglar Resistance	Cooling	EMC Shielding	Battery Compartment
10149-539	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-546	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-547	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-554	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-555	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-562	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-563	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-570	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-571	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-578	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-579	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-586	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-587	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-594	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-595	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-602	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-603	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-610	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional

CatalogNumber	Wall Type	Door Type	Burglar Resistance	Cooling	EMC Shielding	Battery Compartment
10149-611	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-618	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-619	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-626	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-627	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-634	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-635	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-642	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-643	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-650	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-651	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-658	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-659	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-666	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-667	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-674	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-675	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-682	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional

CatalogNumber	Wall Type	Door Type	Burglar Resistance	Cooling	EMC Shielding	Battery Compartment
10149-683	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-690	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-691	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-698	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-699	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-706	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-707	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-714	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-715	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-722	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-723	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-730	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-731	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-738	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-739	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-746	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-747	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-754	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional

CatalogNumber	Wall Type	Door Type	Burglar Resistance	Cooling	EMC Shielding	Battery Compartment
10149-755	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-762	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-763	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-770	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-771	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-778	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-779	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-786	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-787	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-794	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-795	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-802	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-803	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-810	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-811	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-818	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-819	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-826	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional

CatalogNumber	Wall Type	Door Type	Burglar Resistance	Cooling	EMC Shielding	Battery Compartment
10149-827	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-834	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-835	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-842	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-843	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-850	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-851	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-858	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-859	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-866	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional
10149-867	Double Walled	Plain, Triple Door	Optional	Passive	Optional	Optional

Table 3/3

Catalog Number	Finish	Material	Mounting Setup	Package Quantity	Plinth Height
10149-874	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-875	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-882	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-883	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-506	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-507	Powder Coated	Aluminum, Steel	Optional	1	100mm

Catalog Number	Finish	Material	Mounting Setup	Package Quantity	Plinth Height
10149-514	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-515	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-522	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-523	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-530	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-531	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-538	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-539	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-546	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-547	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-554	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-555	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-562	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-563	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-570	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-571	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-578	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-579	Powder Coated	Aluminum, Steel	Optional	1	100mm

Catalog Number	Finish	Material	Mounting Setup	Package Quantity	Plinth Height
10149-586	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-587	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-594	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-595	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-602	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-603	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-610	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-611	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-618	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-619	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-626	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-627	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-634	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-635	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-642	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-643	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-650	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-651	Powder Coated	Aluminum, Steel	Optional	1	100mm

Catalog Number	Finish	Material	Mounting Setup	Package Quantity	Plinth Height
10149-658	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-659	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-666	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-667	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-674	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-675	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-682	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-683	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-690	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-691	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-698	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-699	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-706	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-707	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-714	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-715	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-722	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-723	Powder Coated	Aluminum, Steel	Optional	1	100mm

Catalog Number	Finish	Material	Mounting Setup	Package Quantity	Plinth Height
10149-730	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-731	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-738	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-739	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-746	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-747	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-754	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-755	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-762	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-763	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-770	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-771	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-778	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-779	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-786	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-787	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-794	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-795	Powder Coated	Aluminum, Steel	Optional	1	100mm

Catalog Number	Finish	Material	Mounting Setup	Package Quantity	Plinth Height
10149-802	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-803	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-810	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-811	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-818	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-819	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-826	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-827	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-834	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-835	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-842	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-843	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-850	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-851	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-858	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-859	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-866	Powder Coated	Aluminum, Steel	Optional	1	100mm
10149-867	Powder Coated	Aluminum, Steel	Optional	1	100mm

ADDITIONAL PRODUCT DETAILS

Height dimensions are without base/plinth.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE