


nVent CADDY Pyramid EZ Rubber-Based Adjustable Support



CERTIFICATIONS



FEATURES

Quick height adjustment accommodates for uneven roofs or sloped condensate lines

No tools or fasteners needed; fast snap-on installation

Design sheds water and helps reduce pipe corrosion

Roof-friendly; made of UV-stabilized EPDM material

SPECIFICATIONS

Material: EPDM-SBR Rubber

Table 1/2

Catalog Number	Article Number	NB/DN	Outer Diameter (OD)	Height (H)	Length (L)	Width (W)
RPSE1H24	182365	25	33 mm	45 - 102 mm	102mm	152 mm
RPSE2H46	182375	50	60 mm	102 - 152 mm	102mm	152 mm

CatalogNumber	Article Number	NB/DN	Outer Diameter (OD)	Height (H)	Length (L)	Width (W)
RPSE4H46	182380	100	114 mm	100 - 150 mm	102mm	240 mm


Table 2/2

Catalog Number	Article Number	Unit Weight	Ultimate Static Load (F)
RPSE1H24	182365	0.91 kg	756N
RPSE2H46	182375	1.5 kg	1112N
RPSE4H46	182380	2.33 kg	3920N

ADDITIONAL PRODUCT DETAILS

Ultimate load at 1/4" (6.35 mm) deflection. Contact project or roofing engineer for maximum allowable load on individual project roof system.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

