


# Horizontal Rail, Front, Type R-LD, Rugged, Long Lip , 20 HP

CATALOG NUMBER

**34566-320**



## Combinations of horizontal rails and side panels

$\oplus$  = can be combined,  $\oplus^*$  = combination not recommended

| RAILTYPE   | RAILTYPE 1                                                                        | RAILTYPE 2                                                                        | RAILTYPE 3                                                                        | RAILTYPE 4                                                                        | RAILTYPE 5                                                                        | RAILTYPE 6                                                                        |
|------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|
| RAILTYPE 1 |  | -                                                                                 |  |  |  |  |
| RAILTYPE 2 |  |  |  |  |  |  |
| RAILTYPE 3 |  |  |  |  |  |  |
| RAILTYPE 4 |  |  |  |  |  |  |
| RAILTYPE 5 |  |  |  |  |  |  |
| RAILTYPE 6 |  |  |  |  |  |  |

RAILTYPE 1    RAILTYPE 2    RAILTYPE 3    RAILTYPE 4    RAILTYPE 5    RAILTYPE 6    RAILTYPE 7    RAILTYPE 8    RAILTYPE 9

Side panel    RAILTYPE 1    RAILTYPE 2    RAILTYPE 3    RAILTYPE 4    RAILTYPE 5    RAILTYPE 6    RAILTYPE 7    RAILTYPE 8    RAILTYPE 9

RAILTYPE 1    RAILTYPE 2    RAILTYPE 3    RAILTYPE 4    RAILTYPE 5    RAILTYPE 6    RAILTYPE 7    RAILTYPE 8    RAILTYPE 9

The rugged horizontal rail type can handle shock and vibration up to 25 g. It enables the use of IEEE handles.

## CERTIFICATIONS



## FEATURES

Type R-LD "rugged" horizontal rails with 3-hole fixing for increased robustness

For insertion/extraction of CompactPCI or, VME64x boards

With HP units printed from 28 HP upwards

Length 20, 28, 40, 42, 63, 84 HP or 1000 mm

Aluminum extrusion, anodized finish, conductive contact surface, with HP markings

## PRODUCT ATTRIBUTES

Rack Width: 20HP

Package Quantity: 1

Finish: Anodized

Length: 106.68mm

Material: Aluminum

Product Family: EuropacPRO

Product Type: Horizontal Rail

Type: Rugged, LD

Works With: Subracks

Net Weight: 0.03kg

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**