

Horizontal Rail, Front, Type R-KD, Rugged, Short Lip, 84 HP

Power Utilities

CATALOG NUMBER

34566-284



Combinations of horizontal rails and side panels

 = can be combined.
  = combination not recommended

	Light rail	Frontier F	Heavy rail	Rugged rail
Light rail	-	network F allowed for connection to the network	network F for heavy rail connection to the network	network F supported
Frontier F	+	+	+	+
Heavy rail	+	network F for light rail connection to the network	network F for heavy rail connection to the network	-
Rugged rail	+	+	-	-

Side panel

	Light rail	Frontier F	Heavy rail	Rugged rail
Light rail	+	+	+	+
Frontier F	+	+	+	+
Heavy rail	+	+	+	+
Rugged rail	+	+	+	+

+ can be combined.
 - combination not recommended

The rugged horizontal rail type can handle shock and vibration up to 25 g.

CERTIFICATIONS



FEATURES

Type R-KD "rugged" horizontal rail with 3-hole fixing for increased robustness

Aluminum extrusion, anodized finish, conductive contact surface, with HP markings

PRODUCT ATTRIBUTES

Product Type: Horizontal Rail

Product Family: EuropacPRO

Type: Rugged, KD

Rack Width: 84 HP

Length: 431.8 mm

ADDITIONAL PRODUCT DETAILS

Without M4 thread to front, without printing and without notch for 19" bracket.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE