

# Monitor, Keyboard, Touchpad, 1 U Drawer, German Keyboard

## Data Solutions

### CATALOG NUMBER

---

**60118-581**



Designed for standard 19" rackmount designed for comfort  
robust design for heavy use or harsh environment operation

### CERTIFICATIONS

---



### FEATURES

---

Pull-out 17" TFT color monitor chassis, 1 U (resolution 1280 x 1024; connects to VGA interface)

Keyboard with different language keyboard layout (connects via USB)

Integral touchpad (connects via USB)

Voltage supply: Wide-range input (nominal mains voltage 110 to 240 VAC), Voltage supply 12, 24 and 48 VDC on request

Depth-adjustable mounting for different pitches of server panel/slide mounts; Mounting depth (dimension c = spacing of 19" profiles): dimension c 470 ... 740 mm

### PRODUCT ATTRIBUTES

---

Rack Height: 1U

Package Quantity: 1

Color: Jet Black

Color Code: RAL 9005

Depth: 470mm

Product Type: Cabinet/Rack Drawer

Type: Monitor, Keyboard, Touchpad

Works With: 19" Cabinets

Keyboard Type: QWERTZ

Net Weight: 15.4kg

## ADDITIONAL PRODUCT DETAILS

---

Further versions on request. With trackball or numeric pad.

Other Keyboard layouts see user manual.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE