

Horizontal Rail, Front, Type R-KD, Rugged, Short Lip, 84 HP

Power Utilities

CATALOG NUMBER

34566-284



Combinations of horizontal rails and side panels

+ can be combined - combination not recommended

		Light r.d.	Frontier F	Heavy r.d.	Rugged r.d.
Heavy r.d.		-	network T2 (plastic)	network T2 (plastic)	network T2 (plastic)
Heavy r.d.		+	network T2 (plastic)	network T2 (plastic)	network T2 (plastic)
Light r.d.		+	network T2 (plastic)	network T2 (plastic)	network T2 (plastic)
Horizontal rail		+	network T2 (plastic)	network T2 (plastic)	network T2 (plastic)
Side panel		+	network T2 (plastic)	network T2 (plastic)	network T2 (plastic)

+ can be combined - combination not recommended

The rugged horizontal rail type can handle shock and vibration up to 25 g.

CERTIFICATIONS



FEATURES

Type R-KD "rugged" horizontal rail with 3-hole fixing for increased robustness

Aluminum extrusion, anodized finish, conductive contact surface, with HP markings

PRODUCT ATTRIBUTES

Product Type: Horizontal Rail

Product Family: EuropacPRO

Type: Rugged, KD

Rack Width: 84 HP

Length: 431.8 mm

ADDITIONAL PRODUCT DETAILS

Without M4 thread to front, without printing and without notch for 19" bracket.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE