


Insertor/Extractor Handle Type IET, Grey Lever, Black Button, Bottom, 10 Pieces

CATALOG NUMBER

20817-660



The inserter/extractor handle, type IET in accordance with IEEE 1101.10. Two of these handles can overcome a single lever force of 700 N (per pair).

CERTIFICATIONS



FEATURES

Suitable for insertion and extraction forces up to 700 N (per pair)

In accordance with IEEE 1101.10 and IEC 60297-3-102

A microswitch can be mounted

With locking

Codeable i.a.w. IEEE 1101.10 and IEC 60297-3-103

Package Quantity: 10

Flammability Rating: UL® 94V-0

Complies With: EN 45545-2

Product Type: Handle

Works With: Front Panels

Please order Coding pegs and Microswitch separately.

Technical drawing of a mechanical part, showing three views: top, bottom, and side. The part is a rectangular block with a central slot and a smaller rectangular feature on the side. Dimensions are provided in millimeters.

Top View Dimensions:

- Overall width: 20
- Slot width: 4.07
- Slot depth: 2.54
- Slot position from left edge: 2.54
- Slot position from right edge: 2.54
- Overall height: 7.62

Bottom View Dimensions:

- Overall width: 20
- Slot width: 4.07
- Slot depth: 2.54
- Slot position from left edge: 2.54
- Slot position from right edge: 2.54
- Overall height: 7.62

Side View Dimensions:

- Overall height: 26
- Slot depth: 12.75
- Slot position from bottom edge: 2.5
- Slot position from top edge: 22.75
- Slot width: 4.07
- Slot depth: 2.54
- Slot position from left edge: 2.54
- Slot position from right edge: 2.54
- Overall width: 20

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE