


Insertor/Extractor Handle Type IET, Grey Lever, Black Button, Top, 10 Pieces


CATALOG NUMBER

20817-662



The inserter/extractor handle, type IET in accordance with IEEE 1101.10. Two of these handles can overcome a single lever force of 700 N (per pair).

CERTIFICATIONS



FEATURES

Suitable for insertion and extraction forces up to 700 N (per pair)

In accordance with IEEE 1101.10 and IEC 60297-3-102

A microswitch can be mounted

With locking

Codeable i.a.w. IEEE 1101.10 and IEC 60297-3-103

Package Quantity: 10

Flammability Rating: UL® 94V-0

Complies With: EN 45545-2

Product Type: Handle

Works With: Front Panels

Please order Coding pegs and Microswitch separately.

Technical drawing showing the 'bottom' view of a mechanical part. The drawing includes a perspective view on the left and a detailed orthographic view on the right. The perspective view shows a grey plastic component with a central rectangular opening and two screws. A dimension of 4.07 is indicated for the distance between the screws. The orthographic view shows the component's profile with various dimensions: 2.5, 6.1, 3.6, 2.5, 3.8, 8.95, 6.15, 0.2.95, 26, 12.75, 22.75, 2.5, 4.5, 14, 2.5, 4, 2.54, 2.54, 2.0, and 7.62. The word 'bottom' is written to the left of the orthographic view.

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE