


Insertor/Extractor Handle Type IET, Black Lever, Grey Button, Bottom, 100 Pieces


CATALOG NUMBER

20817-653



The inserter/extractor handle, type IET in accordance with IEEE 1101.10. Two of these handles can overcome a single lever force of 700 N (per pair).

CERTIFICATIONS



FEATURES

Suitable for insertion and extraction forces up to 700 N (per pair)

In accordance with IEEE 1101.10 and IEC 60297-3-102

A microswitch can be mounted

Package Quantity: 100
Handle Type: IET; Bottom Front; Top Rear I/O
Flammability Rating: UL® 94V-0
Color: Black
Complies With: EN 45545-2
Material: Polycarbonate; Zinc Alloy
Product Type: Handle
Type: Inserter/Extractor, Standard
Works With: Front Panels
Gross Weight: 2.256kg

Please order Coding pegs and Microswitch separately.

Technical drawing of the 3000 Series Locking System, showing exploded and assembled views with dimensions.

Exploded View (Top): Shows the handle assembly (1) and the locking mechanism (2) being installed into the door profile. A dimension of 4.07 is indicated for the handle's offset.

Assembled View (Top): Shows the handle and locking mechanism installed in the door profile. Dimensions include: 45 (handle height), 14 (handle offset), 2.5 (profile thickness), 6.1 (handle width), 3.6 (handle offset), 2.5 (profile thickness), 3.8 (handle offset), 12.75 (handle offset), 2.5 (profile thickness), 22.75 (handle offset), 15 (handle offset), 10.52 (handle offset), 26 (handle offset), and 2.95 (handle offset).

Assembled View (Bottom): Shows the handle and locking mechanism installed in the door profile. Dimensions include: 20 (handle height), 2.54 (handle offset), 7.62 (handle offset), 2.54 (handle offset), 4.07 (handle offset), and 2.54 (handle offset).

Assembled View (Side): Shows the handle and locking mechanism installed in the door profile. Dimensions include: 20 (handle height), 2.54 (handle offset), 7.62 (handle offset), 2.54 (handle offset), 4.07 (handle offset), and 2.54 (handle offset).

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE