

PSU 19" AC/DC for CompactPCI Serial, 3 U, 8 HP, 312 W

CATALOG NUMBER

13100-147



Pluggable 19" Power Supply, for CompactPCI applications.
The Power Supply has a wide range AC input, a 12V DC Payload and +5 V DC Standby output.

FEATURES

19" pluggable PSU for CompactPCI Serial applications

Active power factor correction and active current-share function

N+1 redundancy, hot swap

Output signaling: PS present, power failure, PS_ON and enable

I2C interface

High efficiency, > 90% at 220 VAC

PRODUCT ATTRIBUTES

Product Type: Power Supply

Type: 19" Switched-Mode

Works With: CompactPCI Systems

Input Voltage AC: 90 – 264V

Power: 312W

Number of Output Voltages: 2

Voltage 1: 12V

Current 1: 25A

Voltage 2: 5V

Current 2: 2.5A

Rack Height: 3U

Package Quantity: 1

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE