


Insertor/Extractor Handle Type IET, Black Lever, Grey Button, Bottom, 100 Pieces


CATALOG NUMBER

20817-653



The inserter/extractor handle, type IET in accordance with IEEE 1101.10. Two of these handles can overcome a single lever force of 700 N (per pair).

CERTIFICATIONS



FEATURES

Suitable for insertion and extraction forces up to 700 N (per pair)

In accordance with IEEE 1101.10 and IEC 60297-3-102

A microswitch can be mounted

Package Quantity: 100

Flammability Rating: UL® 94V-0

Color: Black

Complies With: EN 45545-2

Material: Polycarbonate; Zinc Alloy

Product Type: Handle

Type: Inserter/Extractor, Standard

Works With: Front Panels

Gross Weight: 2.256kg

Please order Coding pegs and Microswitch separately.

Technical drawing of the front door assembly, showing exploded and assembled views with dimensions.

Exploded View (Top):

- Top view of the door handle assembly.
- Dimensions: 4.07 (height of handle), 2.54 (width of handle), 7.62 (width of base), 2.54 (width of base).

Exploded View (Bottom):

- Bottom view of the door handle assembly.
- Dimensions: 4.07 (height of handle), 2.54 (width of handle), 7.62 (width of base), 2.54 (width of base).

Assembled View (Top):

- Top view of the assembled door handle.
- Dimensions: 4.5 (height of handle), 14 (width of handle), 2.5 (width of base), 6.1 (width of base), 3.8 (width of base), 2.5 (width of base), 3.8 (width of base), 8.55 (width of base), 12.75 (width of base), 22.75 (width of base), 2.5 (width of base), 26 (width of base).

Assembled View (Bottom):

- Bottom view of the assembled door handle.
- Dimensions: 2.5 (width of base), 6.1 (width of base), 3.8 (width of base), 2.5 (width of base), 3.8 (width of base), 8.55 (width of base), 12.75 (width of base), 22.75 (width of base), 2.5 (width of base), 26 (width of base).

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE