

## Plinth Base, MSVS



The plinth allows for cabling without any restrictions. Installing cables is made easy as the plinth creates extra space underneath the enclosure.

### FEATURES

---

Description: Four U-section side pieces fixed by screws to the corner sections. Plinth height 100 mm. Machining is required.

Material: 2 mm AISI 304 / AISI 316L pre-grained stainless steel.

Finish: 400 pre-grained stainless steel.

Pack quantity: 1 plinth with mounting material.

## SPECIFICATIONS

**Thickness:** 2mm

**Finish:** Brushed

Table 1/1

| Catalog Number | E-Number | Height | Width  | Depth | Material             | Enclosure Material |
|----------------|----------|--------|--------|-------|----------------------|--------------------|
| MSVS1103       | 2503266  | 100mm  | 1000mm | 300mm | Stainless Steel 304  | Mild Steel         |
| MSVS1103-316   | 2503267  | 100mm  | 1000mm | 300mm | Stainless Steel 316L | Mild Steel         |
| MSVS1123       | 2503268  | 100mm  | 1200mm | 300mm | Stainless Steel 304  | Mild Steel         |
| MSVS1123-316   | 2503269  | 100mm  | 1200mm | 300mm | Stainless Steel 316L | Mild Steel         |
| MSVS1124       | 2503270  | 100mm  | 1200mm | 400mm | Stainless Steel 304  | Mild Steel         |
| MSVS1124-316   | 2503271  | 100mm  | 1200mm | 400mm | Stainless Steel 316L | Mild Steel         |
| MSVS1063       | 2503260  | 100mm  | 600mm  | 300mm | Stainless Steel 304  | Mild Steel         |
| MSVS1063-316   | 2503261  | 100mm  | 600mm  | 300mm | Stainless Steel 316L | Mild Steel         |
| MSVS1083       | 2503262  | 100mm  | 800mm  | 300mm | Stainless Steel 304  | Mild Steel         |
| MSVS1083-316   | 2503263  | 100mm  | 800mm  | 300mm | Stainless Steel 316L | Mild Steel         |
| MSVS1084       | 2503264  | 100mm  | 800mm  | 400mm | Stainless Steel 304  | Mild Steel         |
| MSVS1084-316   | 2503265  | 100mm  | 800mm  | 400mm | Stainless Steel 316L | Mild Steel         |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**