

4G24 Twist Clip with Stud



CERTIFICATIONS



FEATURES

Supports electrical fixtures from acoustical T-grid

No tools required for installation

Fast, easy and secure twist-on installation

Designed to reduce scratching of T-grid

Nut sold separately

SPECIFICATIONS


Table 1/2

Catalog Number	Article Number	Material	Finish	Color	Screw Length (L)	Flange Thickness (FT)
4G24M11	171680	Spring Steel, Steel	nVent CADDY Armour	Gray	11mm	1.5 mm

Table 2/2

Catalog Number	Article Number	T-Grid Size	Screw Diameter (Sc)	Static Load
4G24M11	171680	24mm	6	220N

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

