


# Telescopic Slide Slim Line, Length 559 mm

## CATALOG NUMBER

**60110-440**



Narrow Telescopic Slide for Subracks with > 100 % extension.

## CERTIFICATIONS



**FEATURES**

---

|                                                            |
|------------------------------------------------------------|
| Suitable for 84 HP width subracks (type F, type H, type L) |
| Locks at full extension                                    |
| Hinged                                                     |
| Extension length > 100 %                                   |
| Rail width 7.5 mm                                          |
| Maximum clear width of extension/drawer w = 84 HP (435 mm) |

**PRODUCT ATTRIBUTES**

---

|                                |
|--------------------------------|
| Length: 559mm                  |
| Package Quantity: 2            |
| Finish: Zinc Plated            |
| Material: Steel                |
| Product Type: Telescopic Slide |
| Static Load: 15kg              |
| Type: Narrow                   |

**ADDITIONAL PRODUCT DETAILS**

---

To mount on 19" plane please order assembly kit separately.

Telescopic slight can only be assembled to a subrack without an assembled rear angle or a modified rear angle (with special cutout).

**WARNING**

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**