

Plug-In Unit Kit With IEL Handle, Shielded, Black, 6 U, 12 HP

CATALOG NUMBER

20848-598

U-shaped front panel for textile gasket
Suitable for insertion and extraction forces up to 700 N (per pair)
Enable the installation of a microswitch
Enable the installation of coding pegs in accordance with IEC 60297-3-103/ IEEE 1101.10

Rack Width: 12HP
Package Quantity: 1
Handle Type: IEL
Mounting: Screw-on Front; Screw-on Rear IO
EMC Gasket Type: Textile
Front Finish: Anodized
Rear Finish: Etched
Treated Edges: No
Complies With: IEC 60297-3-102; IEEE 1101.10; IEC 60297-3-103; IEEE 1101.1/11
EMC Shielding: Yes
Finish: Anodized; Passivated
Height (H): 261.8mm
Material: Aluminum
Product Type: Front Panel
Rack Height: 6U
Type: Front Panel with Handle (PIU)
Width (W): 60.6mm

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE