

# Vertical Pouring Basin, Standard



Standard vertical pouring basins should be used whenever the clearances of the structure allow. The compact size of the standard pouring basins help ensure the best possible flow of filler material.

## FEATURES

Made from heat-resistant graphite

Durable, re-usable and long lasting

Designed for use with T-Series and B-Series vertical sleeves

## SPECIFICATIONS

**Material:** Graphite

Table 1/1

| Catalog Number | Diameter (Ø) | Length 1 (L1) | Length 2 (L2) | Width (W) | Height 1 (H1) | Height 2 (H2) |
|----------------|--------------|---------------|---------------|-----------|---------------|---------------|
| RBWS1500U      | 35 mm        | 137 mm        | 38 mm         | 76 mm     | 124mm         | 70mm          |
| RBWS1500X      | 38 mm        | 137 mm        | 38 mm         | 76 mm     | 124mm         | 70mm          |
| RBWS1481F      | 64 mm        | 152 mm        | 38 mm         | 76 mm     | 159mm         | 95mm          |
| RBWS1481G      | 70 mm        | 152 mm        | 38 mm         | 76 mm     | 159mm         | 95mm          |
| RBWS1481H      | 73 mm        | 152 mm        | 38 mm         | 76 mm     | 159mm         | 95mm          |
| RBWS1481J      | 76 mm        | 152 mm        | 38 mm         | 76 mm     | 159mm         | 95mm          |

| CatalogNumber | Diameter (Ø) | Length 1 (L1) | Length 2 (L2) | Width (W) | Height 1 (H1) | Height 2 (H2) |
|---------------|--------------|---------------|---------------|-----------|---------------|---------------|
| RBWS1481K     | 86 mm        | 152 mm        | 38 mm         | 76 mm     | 159mm         | 95mm          |
| RBWS1482K     | 86 mm        | 165 mm        | 38 mm         | 76 mm     | 191mm         | 108mm         |
| RBWS1482M     | 95 mm        | 165 mm        | 38 mm         | 76 mm     | 191mm         | 108mm         |
| RBWS1499D     | 54 mm        | 149 mm        | 38 mm         | 76 mm     | 140mm         | 76mm          |
| RBWS1499F     | 64 mm        | 149 mm        | 38 mm         | 76 mm     | 140mm         | 76mm          |
| RBWS1499G     | 70 mm        | 149 mm        | 38 mm         | 76 mm     | 140mm         | 76mm          |
| RBWS1499H     | 73 mm        | 149 mm        | 38 mm         | 76 mm     | 140mm         | 76mm          |
| RBWS1500A     | 41 mm        | 137 mm        | 38 mm         | 76 mm     | 124mm         | 70mm          |
| RBWS1500C     | 48 mm        | 137 mm        | 38 mm         | 76 mm     | 124mm         | 70mm          |
| RBWS1500D     | 54 mm        | 137 mm        | 38 mm         | 76 mm     | 124mm         | 70mm          |
| RBWS1500E     | 57 mm        | 137 mm        | 38 mm         | 76 mm     | 124mm         | 70mm          |
| RBWS1500F     | 64 mm        | 137 mm        | 38 mm         | 76 mm     | 124mm         | 70mm          |


## ADDITIONAL PRODUCT DETAILS

RBWS1481, RBWS1482, RBWS1499 and RBWS1500 pouring basins require one RBM2660 pouring basin frame (sold separately).

Prior to installation, please read and understand all of the detailed instructions and safety notices provided in the nVent LENTON Cadweld Rebar Splicing System Instruction Manual.

Sizes not shown may be available by special order. Contact your nVent LENTON representative for more information.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE