


Panhead Screw, Pozidrive

Panhead Screw, Pozidrive.



CERTIFICATIONS



FEATURES

Panhead screw, pozidrive

SPECIFICATIONS

Product Type: Screw

Material: Steel

Table 1/2

Catalog Number	Diameter	Length	Finish	Package Quantity	Thread Size	Product Family
21101-314		5mm	Nickel Plated	100	M2.5	
21101-219		6mm	Nickel Plated	100	M2.5	Frame Type Plug-In Unit
21101-069		8mm	Nickel Plated	100	M2.5	Frame Type Plug-In Unit
21101-221		12mm	Nickel Plated	100	M2.5	Frame Type Plug-In Unit

CatalogNumber	Diameter	Length	Finish	Package Quantity	Thread Size	Product Family
21101-220		10mm	Nickel Plated	100	M2.5	Frame Type Plug-In Unit
21102-024	3mm	6mm	Zinc Plated	100	M3	
21101-222		16mm	Nickel Plated	100	M2.5	Frame Type Plug-In Unit
21100-788		12mm	Zinc Plated	100	M5	EuropacPRO
21120-150	5mm	10mm	Zinc Plated	100	M5	
21100-021	6mm	16mm	Zinc Plated	50	M6	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO
21100-650	6mm	16mm	Zinc Plated	100	M6	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO
21100-022	6mm	16mm	Zinc Plated	100	M6	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO

Table 2/2

Catalog Number	Type	Works With	Thread Type	Quick Ship
21101-314	Panhead Screw	Backplanes, Test Adapters		No
21101-219	Panhead Screw	Backplanes, Test Adapters		No
21101-069	Panhead Screw	Backplanes, Test Adapters		No

Catalog Number	Type	Works With	Thread Type	Quick Ship
21101-221	Panhead Screw	Backplanes, Test Adapters		No
21101-220	Panhead Screw	Backplanes, Test Adapters		No
21102-024	Panhead Screw		Metric	No
21101-222	Panhead Screw	Backplanes, Test Adapters		No
21100-788	Panhead Screw	Subracks		No
21120-150	Coding Block	Cabinet		No
21100-021	Panhead Screw	Front Panels, Eurorack, Novastar, Varistar, Varistar CP		No
21100-650	Panhead Screw	Front Panels, Eurorack, Novastar, Varistar, Varistar CP		No
21100-022	Panhead Screw	Front Panels, Eurorack, Novastar, Varistar, Varistar CP		No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE