


# Rack Angles 19-inch



19-in. U-Shaped Rack Angles are available in square-hole and tapped-hole designs. Tapped Rack Angles have 10-32 tapped holes. Square-Hole Rack Angles are designed to accept metric or English cage nuts. 19-in. Rack Angles are fixed directly into a 600-mm wide enclosure frame. To mount 19-in. Rack Angles in 700- or 800-mm wide frames, use frame reducing brackets.

## FEATURES

---

Furnished in pairs

Tapped-Hole Rack Angles are constructed from 12 gauge conductive steel, while Square-Hole Rack Angles are 14 gauge conductive steel; U-shaped, channel construction

Tapped-Hole Rack Angles have 10-32 threaded holes; Square-Hole Rack Angles are designed to accept metric or English cage nuts. Comply with ANSI/EIA RS-310-D rack mounting standards.

Rack Angles fit directly into 600-mm wide frames; other widths require Frame Reducing Brackets or Adjustable Rack-Mounting Rails (sold separately).

## SPECIFICATIONS

**Finish:** Plated

| Table 1/1      |                |            |            |           |           |            |
|----------------|----------------|------------|------------|-----------|-----------|------------|
| Catalog Number | Article Number | Material   | Rack Units | Hole Type | Thickness | Quick Ship |
| PRA1914TH      | 64890          | Mild Steel | 29U        | Square    | 14ga      | No         |
| PRA1916TH      | 64900          | Mild Steel | 33U        | Square    | 14ga      | No         |
| PRA1918TH      | 64910          | Mild Steel | 38U        | Square    | 14ga      | No         |
| PRA1920TH      | 64920          | Mild Steel | 42U        | Square    | 14ga      | No         |
| PRA1922TH      | 64930          | Mild Steel | 47U        | Square    | 14ga      | No         |
| PRA197TH       | 64880          | Mild Steel | 13U        | Square    | 14ga      | No         |
| PRA198TH       | 40259          | Mild Steel | 16U        | Square    | 14ga      | No         |
| PRA1914TP      | 64960          | Mild Steel | 29U        | Tapped    | 12ga      | No         |
| PRA1916TP      | 64970          | Mild Steel | 33U        | Tapped    | 12ga      | No         |
| PRA1918TP      | 64980          | Mild Steel | 38U        | Tapped    | 12ga      | No         |
| PRA1920TP      | 64990          | Mild Steel | 42U        | Tapped    | 12ga      | No         |
| PRA1922TP      | 65120          | Mild Steel | 47U        | Tapped    | 12ga      | No         |
| PRA197TP       | 64950          | Mild Steel | 13U        | Tapped    | 12ga      | No         |
| PRA198TP       | 40269          | Mild Steel | 16U        | Tapped    | 12ga      | No         |

## ADDITIONAL PRODUCT DETAILS

Vertical holes spaced in 1.75-in. (44.5-mm) increments.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**