


# Front Panel, Front Anodized, Rear Conductive, Shielded, Side Hinged, 6 U, 84 HP

## Power Utilities

### NÚMERO DE CATÁLOGO

**20848-617**



Front panel with textile EMC gasket, side hinged assembly.

### CERTIFICACIONES



### CARACTERÍSTICAS

Front panel with textile EMC gasket

Enables mounting onto the horizontal rails

Suitable for subracks and cases

Hinges can be fitted on left or right

## ATRIBUTOS DEL PRODUCTO

---

Tipo de producto: Panel frontal

Tipo: Panel frontal sin mango

Montaje: Con bisagras, lado

Apantallamiento EMC: No (Retrofitable)

Tipo de junta: Textile

Material: Aluminio

Acabado frontal: Anodizado

Acabado trasero: Conductivo

Bordes tratados: No

Altura del rack: 6 U

Altura: 261.8 mm

Ancho del rack: 84 HP

Anchura: 426.4 mm

Cantidad del paquete: 1

## ADVERTENCIA

---

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Nuestro gran portafolio de marcas:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**