

Horizontal Rail, Front, Type R-KD, Rugged, Short Lip, 84 HP

Power Utilities

NÚMERO DE CATÁLOGO

34566-284



Combinations of horizontal rails and side panels

+ = can be combined, - = combination not recommended

Light r.d.		-	-	-	sidekick r.d. supported
Frontier F		+	sidekick r.d. limited to 1000mm	sidekick r.d. limited to 1000mm	+
Heavy r.d.		+	sidekick r.d. limited to 1000mm	sidekick r.d. limited to 1000mm	+
Rugged r.d.		sidekick r.d. 1500mm	sidekick r.d. 1500mm	-	-
Horizontal rail					
	side panel	1000 r.d.	Frontier F	Heavy r.d.	Rugged r.d.

Light r.d. supported
 1000 r.d. supported
 1500 r.d. supported

The rugged horizontal rail type can handle shock and vibration up to 25 g.

CERTIFICACIONES



CARACTERÍSTICAS

Type R-KD "rugged" horizontal rail with 3-hole fixing for increased robustness

Aluminum extrusion, anodized finish, conductive contact surface, with HP markings

ATRIBUTOS DEL PRODUCTO

Tipo de producto: Carril horizontal

Familia de productos: EuropacPRO

Tipo: Robusto, KD

Ancho del rack: 84 HP

Longitud: 431.8 mm

DETALLES ADICIONALES DEL PRODUCTO

Without M4 thread to front, without printing and without notch for 19" bracket.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Nuestro gran portafolio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE