

PEMSA-kurv Brett for ledning

Data Solutions



PEMSA trådkurv Brett er ryggraden i PEMSAs trådkurv Brettssystemet.

Funksjoner som sørger for sikker installasjon i samsvar med bransjestandarder.

Smart design for å maksimere felteffektiviteten med Rejiband hurtigskjøt.

SERTIFISERINGER



FUNKSJONER

Gir optimal støtte for høyttelses lavspenning- og datakabler

Innovativt Rejiband Rapide installasjonssystem

Samsvar med IEC 61537 belastning og jording

Responsive design- og layouttjenester, inkludert seismikk

SPESIFIKASJONER

Table 1/2

Katalognummer	Artikkelnummer	Farge	Materiale	Avslutt	Lengde (L)	Høyde (H)
WBT35X60S4	821003		Rustfritt stål 304 (en 1,4301)		3000mm	35mm
WBT35X60BA	821001	Svart	Karbonstål	Pulverlakkert	3000mm	35mm

Katalognummer	Artikkelnummer	Farge	Materiale	Avslutt	Lengde (L)	Høyde (H)
WBT35X60EG	821000		Karbonstål	Elektrogalvanisert	3000mm	35mm
WBT35X100BA	821011	Svart	Karbonstål	Pulverlakkert	3000mm	35mm
WBT35X100EG	821010		Karbonstål	Elektrogalvanisert	3000mm	35mm
WBT35X100S4	821013		Rustfritt stål 304 (en 1,4301)		3000mm	35mm
WBT35X150BA	821021	Svart	Karbonstål	Pulverlakkert	3000mm	35mm
WBT35X150EG	821020		Karbonstål	Elektrogalvanisert	3000mm	35mm
WBT35X150S4	821023		Rustfritt stål 304 (en 1,4301)		3000mm	35mm
WBT35X200BA	821031	Svart	Karbonstål	Pulverlakkert	3000mm	35mm
WBT35X200EG	821030		Karbonstål	Elektrogalvanisert	3000mm	35mm
WBT35X200S4	821033		Rustfritt stål 304 (en 1,4301)		3000mm	35mm
WBT35X300BA	821041	Svart	Karbonstål	Pulverlakkert	3000mm	35mm
WBT35X300EG	821040		Karbonstål	Elektrogalvanisert	3000mm	35mm
WBT35X300S4	821043		Rustfritt stål 304 (en 1,4301)		3000mm	35mm
WBT35X400BA	821051	Svart	Karbonstål	Pulverlakkert	3000mm	35mm
WBT35X400EG	821050		Karbonstål	Elektrogalvanisert	3000mm	35mm
WBT35X400S4	821053		Rustfritt stål 304 (en 1,4301)		3000mm	35mm
WBT60X60BA	820001	Svart	Karbonstål	Pulverlakkert	3000mm	60mm
WBT60X60BG	820002	Svart	Karbonstål	Elektrogalvanisert	3000mm	60mm

Katalognummer	Artikkelnummer	Farge	Materiale	Avslutt	Lengde (L)	Høyde (H)
WBT60X60EG	820000		Karbonstål	Elektrogalvanisert	3000mm	60mm
WBT60X60S4	820003		Rustfritt stål 304 (en 1,4301)		3000mm	60mm
WBT60X300BG	820042	Svart	Karbonstål	Elektrogalvanisert	3000mm	60mm
WBT60X300EG	820040		Karbonstål	Elektrogalvanisert	3000mm	60mm
WBT60X300S4	820043		Rustfritt stål 304 (en 1,4301)		3000mm	60mm
WBT60X400BA	820051	Svart	Karbonstål	Pulverlakkert	3000mm	60mm
WBT60X400BG	820052	Svart	Karbonstål	Elektrogalvanisert	3000mm	60mm
WBT60X400EG	820050		Karbonstål	Elektrogalvanisert	3000mm	60mm
WBT60X400S4	820053		Rustfritt stål 304 (en 1,4301)		3000mm	60mm
WBT60X450BA	820081	Svart	Karbonstål	Pulverlakkert	3000mm	60mm
WBT60X450BG	820082	Svart	Karbonstål	Elektrogalvanisert	3000mm	60mm
WBT60X450EG	820080		Karbonstål	Elektrogalvanisert	3000mm	60mm
WBT60X450S4	820083		Rustfritt stål 304 (en 1,4301)		3000mm	60mm
WBT60X500BA	820061	Svart	Karbonstål	Pulverlakkert	3000mm	60mm
WBT60X500BG	820062	Svart	Karbonstål	Elektrogalvanisert	3000mm	60mm
WBT60X500EG	820060		Karbonstål	Elektrogalvanisert	3000mm	60mm
WBT60X500S4	820063		Rustfritt stål 304 (en 1,4301)		3000mm	60mm
WBT60X600BA	820075	Svart	Karbonstål	Pulverlakkert	3000mm	60mm

Katalognummer	Artikkelnummer	Farge	Materiale	Avslutt	Lengde (L)	Høyde (H)
WBT60X600BG	820076	Svart	Karbonstål	Elektrogalvanisert	3000mm	60mm
WBT60X600EG	820074		Karbonstål	Elektrogalvanisert	3000mm	60mm
WBT60X600S4	820077		Rustfritt stål 304 (en 1,4301)		3000mm	60mm
WBT60X100BA	820011	Svart	Karbonstål	Pulverlakkert	3000mm	60mm
WBT60X100BG	820012	Svart	Karbonstål	Elektrogalvanisert	3000mm	60mm
WBT60X100EG	820010		Karbonstål	Elektrogalvanisert	3000mm	60mm
WBT60X100S4	820013		Rustfritt stål 304 (en 1,4301)		3000mm	60mm
WBT60X150BA	820021	Svart	Karbonstål	Pulverlakkert	3000mm	60mm
WBT60X150BG	820022	Svart	Karbonstål	Elektrogalvanisert	3000mm	60mm
WBT60X150EG	820020		Karbonstål	Elektrogalvanisert	3000mm	60mm
WBT60X150S4	820023		Rustfritt stål 304 (en 1,4301)		3000mm	60mm
WBT60X200BA	820031	Svart	Karbonstål	Pulverlakkert	3000mm	60mm
WBT60X200BG	820032	Svart	Karbonstål	Elektrogalvanisert	3000mm	60mm
WBT60X200EG	820030		Karbonstål	Elektrogalvanisert	3000mm	60mm
WBT60X200S4	820033		Rustfritt stål 304 (en 1,4301)		3000mm	60mm
WBT60X300BA	820041	Svart	Karbonstål	Pulverlakkert	3000mm	60mm
WBT100X100BA	823011	Svart	Karbonstål	Pulverlakkert	3000mm	100mm

Katalognummer	Artikkelnummer	Farge	Materiale	Avslutt	Lengde (L)	Høyde (H)
WBT100X100B G	823012	Svart	Karbonstål	Elektrogalvanisert	3000mm	100mm
WBT100X100E G	823010		Karbonstål	Elektrogalvanisert	3000mm	100mm
WBT100X100S 4	823013		Rustfritt stål 304 (en 1,4301)		3000mm	100mm
WBT100X150B A	823021	Svart	Karbonstål	Pulverlakkert	3000mm	100mm
WBT100X150B G	823022	Svart	Karbonstål	Elektrogalvanisert	3000mm	100mm
WBT100X150E G	823020		Karbonstål	Elektrogalvanisert	3000mm	100mm
WBT100X150S 4	823023		Rustfritt stål 304 (en 1,4301)		3000mm	100mm
WBT100X200B A	823031	Svart	Karbonstål	Pulverlakkert	3000mm	100mm
WBT100X200B G	823032	Svart	Karbonstål	Elektrogalvanisert	3000mm	100mm
WBT100X200E G	823030		Karbonstål	Elektrogalvanisert	3000mm	100mm
WBT100X200S 4	823033		Rustfritt stål 304 (en 1,4301)		3000mm	100mm
WBT100X300B A	823041	Svart	Karbonstål	Pulverlakkert	3000mm	100mm
WBT100X300B G	823042	Svart	Karbonstål	Elektrogalvanisert	3000mm	100mm

Katalognummer	Artikkelnummer	Farge	Materiale	Avslutt	Lengde (L)	Høyde (H)
WBT100X300EG	823040		Karbonstål	Elektrogalvanisert	3000mm	100mm
WBT100X300S4	823043		Rustfritt stål 304 (en 1,4301)		3000mm	100mm
WBT100X400BA	823051	Svart	Karbonstål	Pulverlakkert	3000mm	100mm
WBT100X400BG	823052	Svart	Karbonstål	Elektrogalvanisert	3000mm	100mm
WBT100X400EG	823050		Karbonstål	Elektrogalvanisert	3000mm	100mm
WBT100X400S4	823053		Rustfritt stål 304 (en 1,4301)		3000mm	100mm
WBT100X450BA	823081	Svart	Karbonstål	Pulverlakkert	3000mm	100mm
WBT100X450BG	823082	Svart	Karbonstål	Elektrogalvanisert	3000mm	100mm
WBT100X450EG	823080		Karbonstål	Elektrogalvanisert	3000mm	100mm
WBT100X450S4	823083		Rustfritt stål 304 (en 1,4301)		3000mm	100mm
WBT100X500BA	823061	Svart	Karbonstål	Pulverlakkert	3000mm	100mm
WBT100X500BG	823062	Svart	Karbonstål	Elektrogalvanisert	3000mm	100mm
WBT100X500EG	823060		Karbonstål	Elektrogalvanisert	3000mm	100mm

Katalognummer	Artikkelnummer	Farge	Materiale	Avslutt	Lengde (L)	Høyde (H)
WBT100X500S 4	823063		Rustfritt stål 304 (en 1,4301)		3000mm	100mm
WBT100X600B A	823071	Svart	Karbonstål	Pulverlakkert	3000mm	100mm
WBT100X600B G	823072	Svart	Karbonstål	Elektrogalvanis ert	3000mm	100mm
WBT100X600E G	823070		Karbonstål	Elektrogalvanis ert	3000mm	100mm
WBT100X600S 4	823073		Rustfritt stål 304 (en 1,4301)		3000mm	100mm
WBT150X200B A	825031	Svart	Karbonstål	Pulverlakkert	3000mm	150mm
WBT150X200B G	825032	Svart	Karbonstål	Elektrogalvanis ert	3000mm	150mm
WBT150X200E G	825030		Karbonstål	Elektrogalvanis ert	3000mm	150mm
WBT150X200S 4	825033		Rustfritt stål 304 (en 1,4301)		3000mm	150mm
WBT150X300B A	825041	Svart	Karbonstål	Pulverlakkert	3000mm	150mm
WBT150X300B G	825042	Svart	Karbonstål	Elektrogalvanis ert	3000mm	150mm
WBT150X300E G	825040		Karbonstål	Elektrogalvanis ert	3000mm	150mm
WBT150X300S 4	825043		Rustfritt stål 304 (en 1,4301)		3000mm	150mm

Katalognummer	Artikkelnummer	Farge	Materiale	Avslutt	Lengde (L)	Høyde (H)
WBT150X400B A	825051	Svart	Karbonstål	Pulverlakkert	3000mm	150mm
WBT150X400B G	825052	Svart	Karbonstål	Elektrogalvanis ert	3000mm	150mm
WBT150X400E G	825050		Karbonstål	Elektrogalvanis ert	3000mm	150mm
WBT150X400S 4	825053		Rustfritt stål 304 (en 1,4301)		3000mm	150mm
WBT150X450B A	825081	Svart	Karbonstål	Pulverlakkert	3000mm	150mm
WBT150X450B G	825082	Svart	Karbonstål	Elektrogalvanis ert	3000mm	150mm
WBT150X450E G	825080		Karbonstål	Elektrogalvanis ert	3000mm	150mm
WBT150X450S 4	825083		Rustfritt stål 304 (en 1,4301)		3000mm	150mm
WBT150X500B A	825061	Svart	Karbonstål	Pulverlakkert	3000mm	150mm
WBT150X500B G	825062	Svart	Karbonstål	Elektrogalvanis ert	3000mm	150mm
WBT150X500E G	825060		Karbonstål	Elektrogalvanis ert	3000mm	150mm
WBT150X500S 4	825063		Rustfritt stål 304 (en 1,4301)		3000mm	150mm
WBT150X600B A	825071	Svart	Karbonstål	Pulverlakkert	3000mm	150mm

Katalognummer	Artikkelnummer	Farge	Materiale	Avslutt	Lengde (L)	Høyde (H)
WBT150X600BG	825072	Svart	Karbonstål	Elektrogalvanisert	3000mm	150mm
WBT150X600EG	825070		Karbonstål	Elektrogalvanisert	3000mm	150mm
WBT150X600S4	825073		Rustfritt stål 304 (en 1,4301)		3000mm	150mm
WBT150X900BA	825091	Svart	Karbonstål	Pulverlakkert	3000mm	150mm
WBT150X900BG	825092	Svart	Karbonstål	Elektrogalvanisert	3000mm	150mm
WBT150X900EG	825090		Karbonstål	Elektrogalvanisert	3000mm	150mm
WBT150X900S4	825093		Rustfritt stål 304 (en 1,4301)		3000mm	150mm

Table 2/2				
Katalognummer	Artikkelnummer	Bredde (W)	Vekt på enhet	Sertifiseringer
WBT35X60S4	821003	60mm	1.19kg	CE, CADDY EU WBT, UKCA, CADDY EU WBT
WBT35X60BA	821001	60mm	1.2kg	
WBT35X60EG	821000	60mm	1.2kg	CE, CADDY EU WBT, UKCA, CADDY EU WBT
WBT35X100BA	821011	100mm	1.62kg	
WBT35X100EG	821010	100mm	1.62kg	ANOR EU WTB EG S4 BG, CE, CADDY EU WBT, UKCA, CADDY EU WBT
WBT35X100S4	821013	100mm	1.61kg	CE, CADDY EU WBT, UKCA, CADDY EU WBT
WBT35X150BA	821021	150mm	1.76kg	

Katalognummer	Artikkelnummer	Bredde (W)	Vekt på enhet	Sertifiseringer
WBT35X150EG	821020	150mm	1.76kg	CE, CADDY EU WBT, UKCA, CADDY EU WBT, ANOR EU WTB EG S4 BG
WBT35X150S4	821023	150mm	2.12kg	CE, CADDY EU WBT, UKCA, CADDY EU WBT
WBT35X200BA	821031	200mm	2.5kg	
WBT35X200EG	821030	200mm	2.5kg	CE, CADDY EU WBT, UKCA, CADDY EU WBT, ANOR EU WTB EG S4 BG
WBT35X200S4	821033	200mm	3.04kg	ANOR EU WTB EG S4 BG, CE, CADDY EU WBT, UKCA, CADDY EU WBT
WBT35X300BA	821041	300mm	3.42kg	
WBT35X300EG	821040	300mm	3.42kg	CE, CADDY EU WBT, UKCA, CADDY EU WBT, ANOR EU WTB EG S4 BG
WBT35X300S4	821043	300mm	4.13kg	ANOR EU WTB EG S4 BG, CE, CADDY EU WBT, UKCA, CADDY EU WBT
WBT35X400BA	821051	400mm	4.29kg	
WBT35X400EG	821050	400mm	4.29kg	CE, CADDY EU WBT, UKCA, CADDY EU WBT, ANOR EU WTB EG S4 BG
WBT35X400S4	821053	400mm	5.22kg	CE, CADDY EU WBT, UKCA, CADDY EU WBT, ANOR EU WTB EG S4 BG
WBT60X60BA	820001	60mm	2.32kg	
WBT60X60BG	820002	60mm	2.32kg	CE, CADDY EU WBT, UKCA, CADDY EU WBT, ANOR EU WTB EG S4 BG

Katalognummer	Artikkelnummer	Bredde (W)	Vekt på enhet	Sertifiseringer
WBT60X60EG	820000	60mm	2.32kg	ANOR EU WTB EG S4 BG, CE, CADDY EU WBT, UKCA, CADDY EU WBT
WBT60X60S4	820003	60mm	2.32kg	CE, CADDY EU WBT, UKCA, CADDY EU WBT
WBT60X300BG	820042	300mm	5.13kg	DoP, CADDY EU WBT, CE, CADDY EU WBT, UKCA, CADDY EU WBT, ANOR EU WTB EG S4 BG
WBT60X300EG	820040	300mm	5.13kg	ANOR EU WTB EG S4 BG, CE, CADDY EU WBT, UKCA, CADDY EU WBT, DoP, CADDY EU WBT
WBT60X300S4	820043	300mm	5.13kg	CE, CADDY EU WBT, UKCA, CADDY EU WBT, ANOR EU WTB EG S4 BG, DoP, CADDY EU WBT
WBT60X400BA	820051	400mm	6.21kg	
WBT60X400BG	820052	400mm	6.21kg	DoP, CADDY EU WBT, ANOR EU WTB EG S4 BG, CE, CADDY EU WBT, UKCA, CADDY EU WBT
WBT60X400EG	820050	400mm	6.21kg	CE, CADDY EU WBT, UKCA, CADDY EU WBT, ANOR EU WTB EG S4 BG, DoP, CADDY EU WBT
WBT60X400S4	820053	400mm	6.21kg	ANOR EU WTB EG S4 BG, CE, CADDY EU WBT, UKCA, CADDY EU WBT
WBT60X450BA	820081	450mm	6.39kg	
WBT60X450BG	820082	450mm	6.39kg	CE, CADDY EU WBT, UKCA, CADDY EU WBT, ANOR EU WTB EG S4 BG

Katalognummer	Artikkelnummer	Bredde (W)	Vekt på enhet	Sertifiseringer
WBT60X450EG	820080	450mm	6.39kg	ANOR EU WTB EG S4 BG, CE, CADDY EU WBT, UKCA, CADDY EU WBT, DoP, CADDY EU WBT
WBT60X450S4	820083	450mm	6.39kg	
WBT60X500BA	820061	500mm	7.35kg	
WBT60X500BG	820062	500mm	7.35kg	CE, CADDY EU WBT, UKCA, CADDY EU WBT, ANOR EU WTB EG S4 BG
WBT60X500EG	820060	500mm	7.35kg	ANOR EU WTB EG S4 BG, CE, CADDY EU WBT, UKCA, CADDY EU WBT
WBT60X500S4	820063	500mm	7.35kg	CE, CADDY EU WBT, UKCA, CADDY EU WBT, ANOR EU WTB EG S4 BG
WBT60X600BA	820075	600mm	8.43kg	
WBT60X600BG	820076	600mm	8.43kg	ANOR EU WTB EG S4 BG, CE, CADDY EU WBT, UKCA, CADDY EU WBT
WBT60X600EG	820074	600mm	8.43kg	CE, CADDY EU WBT, UKCA, CADDY EU WBT, ANOR EU WTB EG S4 BG
WBT60X600S4	820077	600mm	8.43kg	ANOR EU WTB EG S4 BG, CE, CADDY EU WBT, UKCA, CADDY EU WBT, DoP, CADDY EU WBT
WBT60X100BA	820011	100mm	2.43kg	
WBT60X100BG	820012	100mm	2.43kg	ANOR EU WTB EG S4 BG, DoP, CADDY EU WBT, CE, CADDY EU WBT, UKCA, CADDY EU WBT

Katalognummer	Artikkelnummer	Bredde (W)	Vekt på enhet	Sertifiseringer
WBT60X100EG	820010	100mm	2.43kg	CE, CADDY EU WBT, UKCA, CADDY EU WBT, DoP, CADDY EU WBT, ANOR EU WTB EG S4 BG
WBT60X100S4	820013	100mm	2.43kg	ANOR EU WTB EG S4 BG, CE, CADDY EU WBT, UKCA, CADDY EU WBT, DoP, CADDY EU WBT
WBT60X150BA	820021	150mm	2.6kg	
WBT60X150BG	820022	150mm	2.6kg	DoP, CADDY EU WBT, CE, CADDY EU WBT, UKCA, CADDY EU WBT, ANOR EU WTB EG S4 BG
WBT60X150EG	820020	150mm	2.6kg	ANOR EU WTB EG S4 BG, CE, CADDY EU WBT, UKCA, CADDY EU WBT, DoP, CADDY EU WBT
WBT60X150S4	820023	150mm	2.6kg	CE, CADDY EU WBT, UKCA, CADDY EU WBT, ANOR EU WTB EG S4 BG, DoP, CADDY EU WBT
WBT60X200BA	820031	200mm	3.33kg	
WBT60X200BG	820032	200mm	3.33kg	DoP, CADDY EU WBT, ANOR EU WTB EG S4 BG, CE, CADDY EU WBT, UKCA, CADDY EU WBT
WBT60X200EG	820030	200mm	3.33kg	CE, CADDY EU WBT, UKCA, CADDY EU WBT, ANOR EU WTB EG S4 BG, DoP, CADDY EU WBT
WBT60X200S4	820033	200mm	3.33kg	ANOR EU WTB EG S4 BG, CE, CADDY EU WBT, UKCA, CADDY EU WBT, DoP, CADDY EU WBT
WBT60X300BA	820041	300mm	5.13kg	

Katalognummer	Artikkelnummer	Bredde (W)	Vekt på enhet	Sertifiseringer
WBT100X100BA	823011	100mm	3.27kg	
WBT100X100BG	823012	100mm	3.27kg	CE, CADDY EU WBT, UKCA, CADDY EU WBT, DoP, CADDY EU WBT, ANOR EU WTB EG S4 BG
WBT100X100EG	823010	100mm	3.27kg	DoP, CADDY EU WBT, ANOR EU WTB EG S4 BG, CE, CADDY EU WBT, UKCA, CADDY EU WBT
WBT100X100S4	823013	100mm	3.27kg	CE, CADDY EU WBT, UKCA, CADDY EU WBT, DoP, CADDY EU WBT, ANOR EU WTB EG S4 BG
WBT100X150BA	823021	150mm	3.45kg	
WBT100X150BG	823022	150mm	3.45kg	DoP, CADDY EU WBT, ANOR EU WTB EG S4 BG, CE, CADDY EU WBT, UKCA, CADDY EU WBT
WBT100X150EG	823020	150mm	3.45kg	CE, CADDY EU WBT, UKCA, CADDY EU WBT, DoP, CADDY EU WBT, ANOR EU WTB EG S4 BG
WBT100X150S4	823023	150mm	3.45kg	DoP, CADDY EU WBT, ANOR EU WTB EG S4 BG, CE, CADDY EU WBT, UKCA, CADDY EU WBT
WBT100X200BA	823031	200mm	4.14kg	
WBT100X200BG	823032	200mm	4.14kg	CE, CADDY EU WBT, UKCA, CADDY EU WBT, DoP, CADDY EU WBT, ANOR EU WTB EG S4 BG
WBT100X200EG	823030	200mm	4.14kg	DoP, CADDY EU WBT, ANOR EU WTB EG S4 BG, CE, CADDY EU WBT, UKCA, CADDY EU WBT


Katalognummer	Artikkelnummer	Bredde (W)	Vekt på enhet	Sertifiseringer
WBT100X200S4	823033	200mm	4.14kg	CE, CADDY EU WBT, UKCA, CADDY EU WBT, DoP, CADDY EU WBT, ANOR EU WTB EG S4 BG
WBT100X300BA	823041	300mm	6.15kg	
WBT100X300BG	823042	300mm	6.15kg	DoP, CADDY EU WBT, ANOR EU WTB EG S4 BG, CE, CADDY EU WBT, UKCA, CADDY EU WBT
WBT100X300EG	823040	300mm	6.15kg	CE, CADDY EU WBT, UKCA, CADDY EU WBT, DoP, CADDY EU WBT, ANOR EU WTB EG S4 BG
WBT100X300S4	823043	300mm	6.15kg	DoP, CADDY EU WBT, ANOR EU WTB EG S4 BG, CE, CADDY EU WBT, UKCA, CADDY EU WBT
WBT100X400BA	823051	400mm	7.23kg	
WBT100X400BG	823052	400mm	7.23kg	CE, CADDY EU WBT, UKCA, CADDY EU WBT, DoP, CADDY EU WBT, ANOR EU WTB EG S4 BG
WBT100X400EG	823050	400mm	7.23kg	DoP, CADDY EU WBT, ANOR EU WTB EG S4 BG, CE, CADDY EU WBT, UKCA, CADDY EU WBT
WBT100X400S4	823053	400mm	7.23kg	CE, CADDY EU WBT, UKCA, CADDY EU WBT, DoP, CADDY EU WBT, ANOR EU WTB EG S4 BG
WBT100X450BA	823081	450mm	7.44kg	
WBT100X450BG	823082	450mm	7.44kg	ANOR EU WTB EG S4 BG, CE, CADDY EU WBT, UKCA, CADDY EU WBT

Katalognummer	Artikkelnummer	Bredde (W)	Vekt på enhet	Sertifiseringer
WBT100X450EG	823080	450mm	7.44kg	CE, CADDY EU WBT, UKCA, CADDY EU WBT, DoP, CADDY EU WBT, ANOR EU WTB EG S4 BG
WBT100X450S4	823083	450mm	7.44kg	
WBT100X500BA	823061	500mm	8.34kg	
WBT100X500BG	823062	500mm	8.34kg	ANOR EU WTB EG S4 BG, CE, CADDY EU WBT, UKCA, CADDY EU WBT
WBT100X500EG	823060	500mm	8.34kg	CE, CADDY EU WBT, UKCA, CADDY EU WBT, ANOR EU WTB EG S4 BG
WBT100X500S4	823063	500mm	8.34kg	ANOR EU WTB EG S4 BG, CE, CADDY EU WBT, UKCA, CADDY EU WBT
WBT100X600BA	823071	600mm	9.42kg	
WBT100X600BG	823072	600mm	9.42kg	CE, CADDY EU WBT, UKCA, CADDY EU WBT, ANOR EU WTB EG S4 BG
WBT100X600EG	823070	600mm	9.42kg	ANOR EU WTB EG S4 BG, CE, CADDY EU WBT, UKCA, CADDY EU WBT
WBT100X600S4	823073	600mm	9.42kg	CE, CADDY EU WBT, UKCA, CADDY EU WBT, ANOR EU WTB EG S4 BG
WBT150X200BA	825031	200mm	6.01kg	
WBT150X200BG	825032	200mm	6.01kg	CE, CADDY EU WBT, UKCA, CADDY EU WBT
WBT150X200EG	825030	200mm	6.01kg	CE, CADDY EU WBT, UKCA, CADDY EU WBT, DoP, CADDY EU WBT

Katalognummer	Artikkelnummer	Bredde (W)	Vekt på enhet	Sertifiseringer
WBT150X200S4	825033	200mm	6.01kg	CE, CADDY EU WBT, UKCA, CADDY EU WBT
WBT150X300BA	825041	300mm	7.29kg	
WBT150X300BG	825042	300mm	7.29kg	CE, CADDY EU WBT, UKCA, CADDY EU WBT
WBT150X300EG	825040	300mm	7.29kg	CE, CADDY EU WBT, UKCA, CADDY EU WBT, DoP, CADDY EU WBT
WBT150X300S4	825043	300mm	7.29kg	CE, CADDY EU WBT, UKCA, CADDY EU WBT
WBT150X400BA	825051	400mm	8.47kg	
WBT150X400BG	825052	400mm	8.47kg	CE, CADDY EU WBT, UKCA, CADDY EU WBT
WBT150X400EG	825050	400mm	8.47kg	CE, CADDY EU WBT, UKCA, CADDY EU WBT, DoP, CADDY EU WBT
WBT150X400S4	825053	400mm	8.47kg	CE, CADDY EU WBT, UKCA, CADDY EU WBT
WBT150X450BA	825081	450mm	8.68kg	
WBT150X450BG	825082	450mm	8.68kg	CE, CADDY EU WBT, UKCA, CADDY EU WBT
WBT150X450EG	825080	450mm	8.68kg	CE, CADDY EU WBT, UKCA, CADDY EU WBT
WBT150X450S4	825083	450mm	8.68kg	CE, CADDY EU WBT, UKCA, CADDY EU WBT
WBT150X500BA	825061	500mm	9.7kg	
WBT150X500BG	825062	500mm	9.7kg	CE, CADDY EU WBT, UKCA, CADDY EU WBT
WBT150X500EG	825060	500mm	9.7kg	CE, CADDY EU WBT, UKCA, CADDY EU WBT
WBT150X500S4	825063	500mm	9.7kg	CE, CADDY EU WBT, UKCA, CADDY EU WBT
WBT150X600BA	825071	600mm	10.65kg	

Katalognummer	Artikkelnummer	Bredde (W)	Vekt på enhet	Sertifiseringer
WBT150X600BG	825072	600mm	10.65kg	CE, CADDY EU WBT, UKCA, CADDY EU WBT
WBT150X600EG	825070	600mm	10.65kg	CE, CADDY EU WBT, UKCA, CADDY EU WBT
WBT150X600S4	825073	600mm	10.65kg	CE, CADDY EU WBT, UKCA, CADDY EU WBT
WBT150X900BA	825091	900mm	15.98kg	
WBT150X900BG	825092	900mm	15.98kg	
WBT150X900EG	825090	900mm	15.98kg	
WBT150X900S4	825093	900mm	15.98kg	

DIAGRAMMER



ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.



Vår solide portefølje av merkevarer:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE