

# nVent CADDY Speed Link Light Pack with Nail Gun Bracket



The nVent CADDY Speed Link Light Pack with Nail Gun Bracket includes a precut length (1m and 2m) of 1mm wire rope riveted to an angle bracket designed for direct fastening together with an ultra-low-profile locking device. Contractors can quickly and safely install it to the concrete ceiling using a wide range of nail guns to support and secure lighting and signage.

## VLASTNOSTI

Complete system includes wire, locking device and concrete nail gun insert bracket

Clips onto nozzle of gas or battery-actuated nail guns allowing for hands-off installation at structure or from the floor using a pole

Longer leg angle bracket for tool clearance

Quickly and easily attaches to concrete, steel or composite metal decking

## SPECIFIKACE

**Static Load Safety Factor:** 5:1

**Povrchová úprava:** Electrogalvanized

Table 1/2

| Katalogové číslo | Article Number | Materiál    | Wire Rope Diameter | Wire Rope Length | A     | B       |
|------------------|----------------|-------------|--------------------|------------------|-------|---------|
| CLP1L1GBSF       | 196091         | Ocel, Brass | 1 mm               | 1m               | 38 mm | 25.5 mm |
| CLP1L2GBSF       | 196092         | Ocel, Brass | 1 mm               | 2m               | 38 mm | 25.5 mm |

Table 2/2

| Katalogové číslo | Article Number | Static Load |
|------------------|----------------|-------------|
|------------------|----------------|-------------|

|            |        |      |
|------------|--------|------|
| CLP1L1GBSF | 196091 | 100N |
| CLP1L2GBSF | 196092 | 100N |

**Thickness (T):** 6.5 mm

**Width (W):** 12.5 mm

**Height (H):** 21 mm


**Angle (a):** 60 °

## DALŠÍ PODROBNOSTI O PRODUKTU

Static Load represents the static load of the nail gun insert assembly. Please consult with the nail manufacturer to evaluate the static load of the nail and type of concrete used for the installation. Maximum load is the lesser of the static load from the nail manufacturer or the published load for the assembly.

Nail gun insert is compatible with BeA® CN60-688ES, Hilti® BX 3, GX 3, DEWALT® Trak-It C3, SPIT® PULSA 40E, 800E, 700, 1000 or equivalent nailers.

## DIAGRAMS



## UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na [www.nvent.com](http://www.nvent.com) a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Naše portfolio silných značek:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**

