


nVent CADDY Speed Link SLK with Y-Hook



CERTIFICATIONS



VLASTNOSTI

Complete system includes wire, locking device and two pre-assembled hook end fittings

Fastens to the building structure and hooks to hanging services and tray

Spring latch helps provide secure connection

Convenient design allows one hook to be temporarily detached for maintenance or to add cables to the tray

Single drop with double hook provides increased stability to the system

Also available in a single-hook end fitting configuration

SPECIFIKACE

Wire Rope Diameter:	2 mm
Static Load Safety Factor:	5:1
Povrchová úprava:	Electrogalvanized
Complies With:	SMACNA HVAC-DCS

Table 1/2

Katalogové číslo	Article Number	Materiál	Wire Rope Length	Wire Rope "Y" Length (YL)	A	B
------------------	----------------	----------	------------------	---------------------------	---	---

SLK2YH500L2	196549	Steel, Zinc Alloy, Polypropylene	2m	0.5m	58.4 mm	22.9 mm
SLK2YH500L3	196550	Steel, Zinc Alloy, Polypropylene	3m	0.5m	58.4 mm	22.9 mm
SLK2YH500L7	196551	Steel, Zinc Alloy, Polypropylene	7m	0.5m	58.4 mm	22.9 mm

Table 2/2

Katalogové číslo	Article Number	C	Static Load
SLK2YH500L2	196549	6.4 mm	440N
SLK2YH500L3	196550	6.4 mm	440N
SLK2YH500L7	196551	6.4 mm	440N


Thickness (T): 12.5 mm

Width (W): 19 mm

Height (H): 55 mm

Angle (a): 90 ° Max

DIAGRAMS



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

