


Uniklip Equal Tee



CERTIFICATIONS



VLASTNOSTI

Creates a quick and easy equal tee pathway intersection

Provides optimal support for high-performance low voltage and data cables

Innovative UNIKLIP installation system that installs up to three times faster

IEC 61537 load rating and earthing compliant

No field cutting or modifications required; just drop it in and keep installing the cable tray

Eliminates safety related concerns around field cutting

Tool-free, integrated couplers with Uniklip

SPECIFIKACE

Povrchová úprava: Pregalvanized


Materiál: Ocel

Table 1/1

Katalogové číslo	Article Number	Width (W)	Hloubka (D)	Length (L)	A	B
PCT50X050ET	850300	50 mm	49mm	375mm	202 mm	91 mm

Katalogové číslo	Article Number	Width (W)	Hloubka (D)	Length (L)	A	B
PCT50X075ET	850310	75 mm	49mm	405mm	228 mm	91 mm
PCT50X100ET	850320	100 mm	49mm	425mm	253 mm	91 mm
PCT50X150ET	850330	150 mm	49mm	475mm	303 mm	91 mm
PCT50X225ET	850340	225 mm	49mm	550mm	378 mm	91 mm
PCT50X300ET	850350	300 mm	49mm	625mm	453 mm	91 mm
PCT50X450ET	850360	450 mm	49mm	775mm	603 mm	91 mm
PCT50X500ET	850370	500 mm	49mm	852mm	653 mm	91 mm
PCT50X600ET	850380	600 mm	49mm	925mm	753 mm	91 mm

DIAGRAMS



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

