

Outdoor Comline FTTX Cabinet

Data Solutions



Telecom applications require sophisticated electronics in outdoor setups. nVent SCHROFF Outdoor cabinets shield such electronic components from extreme weather, Vandalism and thereby ensuring operational continuity. nVent SCHROFF cabinets can be used as Dslam / Point of Presence / Zone pooling / FTTC / FTTH / MFG cabinets.

CERTIFICATIONS



VLASTNOSTI

Height dimensions without plinth (140 mm)

Single wall, lightweight aluminium cabinet

Insulated cabinet

IP 55

SPECIFIKACE

Materiál: Hliník

Table 1/3

Katalogové číslo	Product Type	Produktová řada	Rack Height	Výška	Šířka	Hloubka
12349-007	Outdoor Cabinet	Comline FTTX	12U	600mm	800mm	600mm

Katalogové číslo	Product Type	Produktová řada	Rack Height	Výška	Šířka	Hloubka
12349-006	Outdoor Cabinet	Comline FTTX	25U	1200mm	800mm	600mm
12349-005	Outdoor Cabinet	Comline FTTX	12U	600mm	800mm	600mm
12349-008	Outdoor Cabinet	Comline FTTX	25U	1200mm	800mm	600mm

Table 2/3

Katalogové číslo	Wall Type	Door Type	Access	Cooling	EMC Shielding	Complies With
12349-007	Single Walled	Single Door	Front, Back	Insulation	No	IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160
12349-006	Single Walled	Single Door	Front, Back	Insulation	No	IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160
12349-005	Single Walled	Single Door	Front, Back	Insulation	No	IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160
12349-008	Single Walled	Single Door	Front, Back	Insulation	No	IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160

Table 3/3

Katalogové číslo	Množství v balení	Povrchová úprava
------------------	-------------------	------------------

12349-007	1	Strukturovaný Práškový
12349-006	1	Strukturovaný Práškový
12349-005	1	Strukturovaný Práškový
12349-008	1	Strukturovaný Práškový

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE