


Water Pipe Ground Clamp



The nVent ERICO Water Pipe Ground Clamp provides a highly reliable method for grounding copper conductors to metallic water pipes or ground rods, essential for electrical safety in residential, commercial, and industrial systems. Constructed from high-strength silicone bronze, this clamp ensures excellent durability, corrosion resistance, and secure, long-lasting electrical connections. Its robust design makes it a trusted component for creating effective grounding paths in accordance with applicable electrical codes and standards.

CERTIFICATIONS



VLASTNOSTI

Manufactured from high-strength silicone bronze for superior durability and corrosion resistance

Used for connecting copper conductors to metallic water pipe or ground rods

Designed for effectively connecting copper conductors to metallic water pipes or ground rods

Ensures a secure and low-resistance path for grounding applications

Suitable for a range of conductor and pipe sizes

SPECIFIKACE


Materiál: Silicon Bronze

Table 1/1

Katalogové číslo	Article Number	Pipe Size, Nominal (Ø)	Pipe Size, Actual (Ø)	Certifications
CWP1JJ	710262	1/2" - 1"	12.7 - 25.4 mm	
CWP1JU	710266	1/2" - 1"	12.7 - 25.4 mm	CSA, UL, cUL

Katalogové číslo	Article Number	Pipe Size, Nominal (Ø)	Pipe Size, Actual (Ø)	Certifications
CWP4J	710264	2 1/2" - 4"	63.5 - 101.6 mm	CSA, UL, cUL

DIAGRAMS



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

⚠ WARNING: This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE