

nVent ERICO Cadweld Plus Welding Material, F80



VLASTNOSTI

Mixture consists mainly of copper oxide and aluminum

Primarily used in making connections to load-bearing rail

Integrated welding material package

Welding material is color coded with a yellow cover and engineered for railway and railway property applications

Outer ring of the yellow cover is color-coded by size for ease of identification to prevent misapplication

Electronic ignition

No starting material required

Non-explosive

Not subject to spontaneous ignition

See specific nVent ERICO Cadweld connection details to determine welding material requirements

SPECIFIKACE

Table 1/1

Katalogové číslo	Article Number	Color Code Ring
PB400PLUSF80	165736	Brown
PB150PLUSF80	165732	Dark Blue
PB65PLUSF80	165729	Dark Green

Katalogové číslo	Article Number	Color Code Ring
PB90PLUSF80	165730	Gray
PB45PLUSF80	165728	Light Blue
PB300PLUSF80	165735	Light Green
PB115PLUSF80	165731	Orange
PB250PLUSF80	165734	Purple
SB32PLUSF80		White
PB200PLUSF80	165733	Yellow

DALŠÍ PODROBNOSTI O PRODUKTU

nVent ERICO Cadweld Plus welding material requires electronic control unit for ignition (sold separately).

All nVent ERICO Cadweld connections on rail properties must be installed using either nVent ERICO Cadweld Welding Material, Rail F80 or nVent ERICO Cadweld Plus Welding Material, F80.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

 **WARNING:** This product can expose you to chemicals including silica, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE