

T-Series Horizontal Fixed Angle Splice Kit, Top Fill, 15-30°



T-Series splice kits contain the following: Sleeve, filler material kit (filler material, packing, pouring basin ceramic insert and disk, pouring basin ceramic guide tube), pouring basin and pouring basin crucible. Splice kits are ordered based on the quantity of splices needed. Sleeves and filler material kits are one-time use parts. Pouring basins and crucibles are prorated based on their anticipated life. Ordering splice kits simplifies ordering, reduces order errors and helps ensure proper sizing of components. Kits can be ordered with longer (extended) sleeves for use when the reinforcing steel deformation pattern or spacing does not meet the minimum product specifications.

VLASTNOSTI

Simplifies ordering

Used to splice the same diameter bars

SPECIFIKACE

Sleeve: Standard Length

Table 1/2

Katalogové číslo	Angle (a)	Rebar Size, Metric	Rebar Size, US	Rebar Size, Canada	Length 1 (L1)	Length 2 (L2)
RBT109130H	30 °	32 mm	#10		165 mm	285 mm
RBT1110115H	15 °	36 mm	#11	35M	167 mm	301 mm
RBT1110130H	30 °	36 mm	#11	35M	172 mm	285 mm
RBT189115H	15 °	57 mm	#18	55M	208 mm	301 mm
RBT189130H	30 °	57 mm	#18	55M	213 mm	285 mm

Table 2/2

Katalogové číslo	Height 1 (H1)	Height 2 (H2)	Diameter (Ø)
RBT109130H	496mm	175mm	127 mm
RBT1110115H	506mm	138mm	127 mm
RBT1110130H	496mm	200mm	127 mm
RBT189115H	538mm	150mm	178 mm
RBT189130H	528mm	207mm	178 mm

DALŠÍ PODROBNOSTI O PRODUKTU


Prior to installation, please read and understand all of the detailed instructions and safety notices provided in the nVent LENTON Cadweld Rebar Splicing System instruction manual.

All dimensions are for reference only.

Components can also be purchased separately: (1) Sleeve, (2) Filler Material Kit (filler material, packing, pouring basin ceramic insert and disk, pouring basin ceramic guide tube), (3) Pouring Basin, and (4) Pouring Basin Crucible.

Splice Kit Components							
Splice Kit	Filler Material	Packing (2 Required)	Pouring Basin Ceramic Insert and Disk	Pouring Basin Ceramic Guide Tube	Sleeve	Pouring Basin	Pouring Basin Crucible
RBT109130H	RBF90	RBS354712	RBS5037	RBS5038	RBT1091HA	RBWS2223E	RBWS22775
RBT1110115H	RBF105	RBS354712	RBS5037	RBS5038	RBT11101HA	RBWS2222F	RBWS22775
RBT1110130H	RBF105	RBS354712	RBS5037	RBS5038	RBT11101HA	RBWS2223F	RBWS22775
RBT189115H	RBF270	RBS354720	RBS5037	RBS5039	RBT1891HA	RBWS2222M	RBWS22777
RBT189130H	RBF270	RBS354720 RBS354720	RBS5037	RBS5039	RBT1891HA	RBWS2223M	RBWS22777

DIAGRAMS



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE