

90° koleno čistého žlabu



Clean Tray 90-Degree Elbows are used for right-angle installations. The Clean Tray stainless steel system is designed to protect rated cabling in applications that require frequent washdown.

VLASTNOSTI

Clean Tray 90-Degree Elbows are used for right-angle installations

The Clean Tray stainless steel system is designed to protect rated cabling in applications that require frequent washdown

SPECIFIKACE

Povrchová úprava: Brushed #3
Materiál: Stainless Steel 304

Table 1/1

Katalogové číslo	Typ	Výška	Šířka	Tloušťka	Rychlé odeslání
CT22EFC90SS	Elbow	51mm	51mm	1.27mm	Ne
CT22EFCNT90SS	Elbow	51mm	51mm	1.27mm	Ne
CT22EIC90SS	Elbow	51mm	51mm	1.27mm	Ne
CT22EOC90SS	Elbow	51mm	51mm	1.27mm	Ne
CT22PEFC90SS	Elbow	51mm	51mm	1.27mm	Ne
CT33EFC90SS	Elbow	76mm	76mm	1.27mm	Ne
CT33EIC90SS	Elbow	76mm	76mm	1.27mm	Ne
CT33EOC90SS	Elbow	76mm	76mm	1.27mm	Ne
CT44EFC90SS	Elbow	102mm	102mm	1.27mm	Ne
CT44EFCNT90SS	Elbow	102mm	102mm	1.27mm	Ne
CT44EIC90SS	Elbow	102mm	102mm	1.27mm	Ne
CT44EOC90SS	Elbow	102mm	102mm	1.27mm	Ne
CT44PEFC90SS	Elbow	102mm	102mm	1.27mm	Ne
CT46EFC90SS	Elbow	102mm	152mm	1.27mm	Ne
CT46EIC90SS	Elbow	102mm	152mm	1.27mm	Ne
CT46EOC90SS	Elbow	102mm	152mm	1.27mm	Ne
CT66EFC90SS	Elbow	152mm	152mm	1.27mm	Ne

Katalogové číslo	Typ	Výška	Šířka	Tloušťka	Rychlé odeslání
CT66EFCNT90SS	Elbow	152mm	152mm	1.27mm	Ne
CT66EIC90SS	Elbow	152mm	152mm	1.27mm	Ne
CT66EOC90SS	Elbow	152mm	152mm	1.27mm	Ne
CTS33EFC90SS	Elbow	76mm	76mm	1.27mm	Ne
CTS33PEFC90SS	Elbow	76mm	76mm	1.27mm	Ne
CTS44EFC90SS	Elbow	102mm	102mm	1.27mm	Ne
CTS44PEFC90SS	Elbow	102mm	102mm	1.27mm	Ne
CTS46EFC90SS	Elbow	102mm	152mm	1.27mm	Ne
CTS46PEFC90SS	Elbow	102mm	152mm	1.27mm	Ne
CTS66EFC90SS	Elbow	152mm	152mm	1.27mm	Ne
CTS66PEFC90SS	Elbow	152mm	152mm	1.27mm	Ne
CT33EFCNT90SS	Elbow	76mm	76mm	1.27mm	Ne
CT33PEFC90SS	Elbow	76mm	76mm	1.27mm	Ne
CT46EFCNT90SS	Elbow	102mm	152mm	1.27mm	Ne
CT46PEFC90SS	Elbow	102mm	152mm	1.27mm	Ne
CT66PEFC90SS	Elbow	152mm	152mm	1.27mm	Ne

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE