


# EuropacPRO 19" Subrack Kit for Backplane, Shielded

## Power Utilities

EMC Shielded subrack for backplane mounting, rear side covered by a rear panel.



### CERTIFICATIONS

---



### VLASTNOSTI

---

Subrack with side panel type F ("flexible"), front 19" bracket included, depth-adjustable 19" bracket sold separately (not included in items delivered)

Supplied as space-saving flat-pack

Modifications such as cutouts, different finishes or dimensions available

EMC of approximately 40 dB at 1 GHz, 30 dB at 2 GHz, assuming that the front is covered with shielded front panels, testing in accordance with VG 95373 part 15

IP 20, in accordance with IEC 60529

Aluminum construction

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Rear horizontal rail for backplane mounting with insulation strip

Horizontal rail type "light"

## SPECIFIKACE

**Product Type:** Subrack/Chassis

Table 1/2

Katalogové číslo	Rack Height	Hloubka	Množství v balení	For Mounting	Board Depth	Rukojeť v ceně
24563-142	3 U	235 mm	1	Backplane	160 mm, 220 mm	No
24563-143	3 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	No
24563-144	3 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm	No
24563-145	3 U	415 mm	1	Backplane	160 mm, 220 mm, 280 mm	No
24563-146	3 U	475 mm	1	Backplane	160 mm, 220 mm, 280 mm	No
24563-442	6 U	235 mm	1	Backplane	160 mm, 220 mm	No
24563-443	6 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	No
24563-444	6 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm	No
24563-445	6 U	415 mm	1	Backplane	160 mm, 220 mm, 280 mm	No
24563-446	6 U	475 mm	1	Backplane	160 mm, 220 mm, 280 mm	No

Table 2/2

Katalogové číslo	Mounting	Complies With	EMC Shielding	Rack Width	Static Load
24563-142	Rack	IEC 60297-3-103	Yes	84 HP	11 kgf
24563-143	Rack	IEC 60297-3-103	Yes	84 HP	11 kgf
24563-144	Rack	IEC 60297-3-103	Yes	84 HP	11 kgf
24563-145	Rack	IEC 60297-3-103	Yes	84 HP	11 kgf
24563-146	Rack	IEC 60297-3-103	Yes	84 HP	11 kgf

Katalogové číslo	Mounting	Complies With	EMC Shielding	Rack Width	Static Load
24563-442	Rack	IEC 60297-3-103	Yes	84 HP	11 kgf
24563-443	Rack	IEC 60297-3-103	Yes	84 HP	11 kgf
24563-444	Rack	IEC 60297-3-103	Yes	84 HP	11 kgf
24563-445	Rack	IEC 60297-3-103	Yes	84 HP	11 kgf
24563-446	Rack	IEC 60297-3-103	Yes	84 HP	11 kgf

## DALŠÍ PODROBNOSTI O PRODUKTU

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

## UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na [www.nvent.com](http://www.nvent.com) a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**