

BEP Bar End Protector



Bar end protectors are placed onto the ends of threaded reinforcing steel bars. These protective caps help prevent damage to the nVent LENTON threads and help keep dirt and water out of the threads during storage, transportation and installation.

VLASTNOSTI

Easy to install and remove

Color coded for the appropriate reinforcing bar size

SPECIFIKACE

Table 1/1

Katalogové číslo	Article Number	Rebar Size, Metric	Rebar Size, US	Rebar Size, Canada	Barva
EL10BTP	370000	10 mm	#3		Yellow
EL12BTP	370010	12 mm	#4	10M	Red
EL14BTP	370020	14 mm			Green
EL16BTP	370060	16 mm	#5	15M	Black
EL18BTP	370130	18 mm			White
EL20BTP	370070	20 mm	#6	20M	Yellow
EL22BTP	370140	22 mm	#7		Blue

Katalogové číslo	Article Number	Rebar Size, Metric	Rebar Size, US	Rebar Size, Canada	Barva
EL25BTP	370080	25 mm	#8	25M	Red
EL28BTP	370090	28 mm	#9	30M	Black
EL30BTP	370100	30 mm			White
EL32BTP	370150	32 mm	#10		Yellow
EL34BTP	370160	34 mm			Red
EL36BTP	370110	36 mm	#11	35M	Blue
EL38BTP	370170	38 mm	#12		White
EL40BTP	370120	40 mm			Green
EL43TBTP	370180	43 mm	#14	45M	Red
EL50TBTP	370190	50 mm			Black
EL57TBTP	370200	57 mm	#18	55M	Blue

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE