


Front Handle One-Piece, Width 12.2 mm

Power Utilities



The handle can be assembled to a subrack or 19" front panel. Available with clear or black anodized surface. Handles will be bolted from the rear side.

CERTIFICATIONS



VLASTNOSTI

Static load-carrying capacity 30 kg/pair

Bolted from rear

SPECIFIKACE

Table 1/2

Katalogové číslo	Rack Height	Množství v balení	Typ rukojeti	Barva	Materiál	Produktová řada
10501-116	1 U	1	Straight	Silver	Hliník	EuropacPRO
10501-004	2 U	1	Straight	Silver	Hliník	EuropacPRO
10501-020	3 U	1	Angled Handle	Silver	Hliník	EuropacPRO

Katalogové číslo	Rack Height	Množství v balení	Typ rukojeti	Barva	Materiál	Produktová řada
10501-026	3 U	1	Straight	Black	Hliník	EuropacPRO
10501-005	3 U	1	Straight	Silver	Hliník	EuropacPRO
10501-006	4 U	1	Straight	Silver	Hliník	EuropacPRO
10501-007	5 U	1	Straight	Silver	Hliník	EuropacPRO
10501-022	6 U	1	Angled Handle	Silver	Hliník	EuropacPRO
10501-029	6 U	1	Straight	Black	Hliník	EuropacPRO
10501-008	6 U	1	Straight	Silver	Hliník	EuropacPRO
10501-016	2 U	1	Straight	Silver	Hliník	EuropacPRO
10501-021	4 U	1	Angled Handle	Silver	Hliník	EuropacPRO
10501-018	4 U	1	Straight	Silver	Hliník	EuropacPRO
10501-025	2 U	1	Straight	Black	Hliník	EuropacPRO
10501-027	4 U	1	Straight	Black	Hliník	EuropacPRO
10501-028	5 U	1	Straight	Black	Hliník	EuropacPRO

Table 2/2

Katalogové číslo	Product Type	Works With	Torque
10501-116	Handle	Subracks	
10501-004	Handle	Subracks	
10501-020	Handle	Subracks	2.4 N·m
10501-026	Handle	Subracks	2.4 N·m

Katalogové číslo	Product Type	Works With	Torque
10501-005	Handle	Subracks	2.4 N·m
10501-006	Handle	Subracks	
10501-007	Handle	Subracks	
10501-022	Handle	Subracks	2.4 N·m
10501-029	Handle	Subracks	2.4 N·m
10501-008	Handle	Subracks	2.4 N·m
10501-016	Handle	Subracks	
10501-021	Handle	Subracks	2.4 N·m
10501-018	Handle	Subracks	2.4 N·m
10501-025	Handle	Subracks	
10501-027	Handle	Subracks	
10501-028	Handle	Subracks	

DALŠÍ PODROBNOSTI O PRODUKTU

Please order assembly part kit separately.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE