

Guide Rail With Coding, preassembled ESD Clip for CompactPCI/ VME64x, PC

Power Utilities

VLASTNOSTI

NEW generation with coding type plastic guide rails for reliable retention of PCBs or plug-in units

Significantly increased stability, due to an optimized design and high quality material (PC)

Improved fire safety properties, fulfills EN 45545-2 requirement sets R22, R23 and R24 with HL3

"Halogen-Free", according to IEC 61249-2-21

Can be clipped into horizontal rails (Al extrusion) or into 1.5 mm thick plates

Can be bolted to the horizontal rails Type H and R for higher shock and vibration requirements

ESD clip for an conductive contact between PCB and horizontal rail preassembled

Storage temperature: from -40 °C ... 130 °C

SPECIFIKACE

Table 1/2

Katalogové číslo	Barva	Množství v balení	Board Depth	Groove Width	Complies With	Materiál
24568-847	Red	10	160 mm	2	EN 45545-2	Polycarbonate
24568-848	Grey	10	160 mm	2	EN 45545-2	Polycarbonate
24568-850	Red	10	160 mm	2	EN 45545-2	Polycarbonate
24568-851	Grey	10	160 mm	2	EN 45545-2	Polycarbonate
24568-853	Red	10	70 mm	2	EN 45545-2	Polycarbonate

Katalogové číslo	Barva	Množství v balení	Board Depth	Groove Width	Complies With	Materiál
24568-854	Grey	10	70 mm	2	EN 45545-2	Polycarbonate
24568-855	Red	10	70 mm	2	EN 45545-2	Polycarbonate
24568-856	Grey	10	70 mm	2	EN 45545-2	Polycarbonate

Table 2/2				
Katalogové číslo	Produktová řada	Product Type	Typ	Works With
24568-847	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding and preassembled ESD Clips	Subracks, Cases, 19" Chassis, Systems
24568-848	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding and preassembled ESD Clips	Subracks, Cases, 19" Chassis, Systems
24568-850	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding and preassembled ESD Clips	Subracks, Cases, 19" Chassis, Systems
24568-851	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding and preassembled ESD Clips	Subracks, Cases, 19" Chassis, Systems
24568-853	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding and preassembled ESD Clips	Subracks, Cases, 19" Chassis, Systems
24568-854	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding and preassembled ESD Clips	Subracks, Cases, 19" Chassis, Systems

Katalogové číslo	Produktová řada	Product Type	Typ	Works With
24568-855	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding and preassembled ESD Clips	Subracks, Cases, 19" Chassis, Systems
24568-856	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding and preassembled ESD Clips	Subracks, Cases, 19" Chassis, Systems

DALŠÍ PODROBNOSTI O PRODUKTU

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE