

Interscale 19" Rack Mount Chassis, Perforated

Power Utilities



Flexible 19" Chassis with integrated EMC protection and perforated side. Based on the nVent SCHROFF Interscale platform and developed in accordance with IEC 60297-3-109.

CERTIFICATIONS



VLASTNOSTI

Modular desktop case consisting of 4 assembled parts, with perforated sides

Developed according to IEC 60297-3-109 (under progress at IEC)

Integrated EMC protection

Ingress protection up to IP 20

Color RAL 7016

Modified or customized cases upon request

SPECIFIKACE

Table 1/2

Katalogové číslo	Rack Height	Hloubka	Množství v balení	Usable Width	Mounting	Complies With
14826-105	1 U	221 mm	1	444 mm	Rack	IEC 60297-3-100

Katalogové číslo	Rack Height	Hloubka	Množství v balení	Usable Width	Mounting	Complies With
14826-107	1 U	310 mm	1	444 mm	Rack	IEC 60297-3-100
14826-307	3 U	310 mm	1	444 mm	Rack	IEC 60297-3-100
14826-205	2 U	221 mm	1	444 mm	Rack	IEC 60297-3-100
14826-207	2 U	310 mm	1	444 mm	Rack	IEC 60297-3-100
14826-305	3 U	221 mm	1	444 mm	Rack	IEC 60297-3-100

Table 2/2

Katalogové číslo	EMC Shielding	Produktová řada	Product Type	Typ
14826-105	Yes	Interscale	Small Form Factor Case	Perforated
14826-107	Yes	Interscale	Small Form Factor Case	Perforated
14826-307	Yes	Interscale	Small Form Factor Case	Perforated
14826-205	Yes	Interscale	Small Form Factor Case	Perforated
14826-207	Yes	Interscale	Small Form Factor Case	Perforated
14826-305	Yes	Interscale	Small Form Factor Case	Perforated

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE