

Varistar CP 19" Swing Frame Trim

Power Utilities

Varistar CP swing frame provides optimum space usage inside the rack. The swing frames come with handles.

VLASTNOSTI

Includes handle and cut-out for cable eyes

To cover the gap between swing frame and cabinet upright for 800 mm wide cabinets

Maximum swing bracket: 120 or 160

For swing frame with load-carrying capacity 150 kg, a stop is recommended for security reasons

Locking no. 333

Spare key for DIN semi-profile cylinder

SPECIFIKACE

Table 1/2

Katalogové číslo	Rack Height	Barva	Kód barvy	Materiál	Product Type	Stupeň krytí
21630-746	24 U	Black Grey	RAL 7021	Ocel	Cabinet/Rack Frame	IP20
21630-749	24 U	Black Grey	RAL 7021	Ocel	Cabinet/Rack Frame	IP20
21630-747	33 U	Black Grey	RAL 7021	Ocel	Cabinet/Rack Frame	IP20
21630-750	33 U	Black Grey	RAL 7021	Ocel	Cabinet/Rack Frame	IP20
21630-751	42 U	Black Grey	RAL 7021	Ocel	Cabinet/Rack Frame	IP20
21630-748	42 U	Black Grey	RAL 7021	Ocel	Cabinet/Rack Frame	IP20

Table 2/2

Katalogové číslo	Typ	Works With
------------------	-----	------------

21630-746	Swing	Varistar, Varistar CP
21630-749	Swing	Varistar, Varistar CP
21630-747	Swing	Varistar, Varistar CP
21630-750	Swing	Varistar, Varistar CP
21630-751	Swing	Varistar, Varistar CP
21630-748	Swing	Varistar, Varistar CP

DALŠÍ PODROBNOSTI O PRODUKTU

Varistar CP swing frame provides optimum space usage inside the rack. The swing frames come with handles.

Please purchase the grounding kit separately.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE