

Varistar CP Cabinet Frame, Seismic Heavy Load

Power Utilities

Welded, steel enclosure engineered specifically to protect equipment in areas with seismic activity and satisfy Bellcore Zore 4 requirements.

VLASTNOSTI

St, 1.5 mm, zinc-plated, finish: powder-coated

Earthquake resistance to Bellcore Zone 4

Welded heavy-duty frame with strengthening brackets, RAL 7021

Dynamic load-carrying capacity 500 kg to IEC 61587-2

SPECIFIKACE

Table 1/3

Katalogové číslo	Rack Height	Výška	Šířka	Hloubka	Shock and Vibration Tolerance	Barva
20630-269	42 U	2000 mm	600 mm	1000 mm	5 g (force)	Black Grey
20630-270	42 U	2000 mm	600 mm	1200 mm	5 g (force)	Black Grey
20630-271	42 U	2000 mm	800 mm	1000 mm	5 g (force)	Black Grey
20630-272	42 U	2000 mm	800 mm	1200 mm	5 g (force)	Black Grey
20630-273	33 U	1600 mm	600 mm	600 mm	5 g (force)	Black Grey
20630-274	33 U	1600 mm	600 mm	800 mm	5 g (force)	Black Grey
20630-275	33 U	1600 mm	800 mm	600 mm	5 g (force)	Black Grey

Katalogové číslo	Rack Height	Výška	Šířka	Hloubka	Shock and Vibration Tolerance	Barva
20630-276	33 U	1600 mm	800 mm	800 mm	5 g (force)	Black Grey
20630-277	38 U	1800 mm	600 mm	600 mm	5 g (force)	Black Grey
20630-278	38 U	1800 mm	800 mm	600 mm	5 g (force)	Black Grey
20630-279	38 U	1800 mm	800 mm	600 mm	5 g (force)	Black Grey
20630-280	38 U	1800 mm	800 mm	800 mm	5 g (force)	Black Grey
20630-281	42 U	2000 mm	600 mm	600 mm	5 g (force)	Black Grey
20630-282	42 U	2000 mm	600 mm	800 mm	5 g (force)	Black Grey
20630-283	42 U	2000 mm	800 mm	600 mm	5 g (force)	Black Grey
20630-284	42 U	2000 mm	800 mm	1600 mm	5 g (force)	Black Grey
20630-285	42 U	2200 mm	600 mm	600 mm	5 g (force)	Black Grey
20630-286	47 U	2200 mm	600 mm	800 mm	5 g (force)	Black Grey
20630-287	47 U	2200 mm	800 mm	600 mm	5 g (force)	Black Grey
20630-288	47 U	2200 mm	800 mm	800 mm	5 g (force)	Black Grey

Table 2/3

Katalogové číslo	Kód barvy	Complies With	Frame Material	Materiál	Product Type	Static Load
20630-269	RAL 7021	IEC 61587-1, IEC 61587-2	Ocel	Ocel	Cabinet/Rack Frame	1600 kgf
20630-270	RAL 7021	IEC 61587-1, IEC 61587-2	Ocel	Ocel	Cabinet/Rack Frame	1600 kgf
20630-271	RAL 7021	IEC 61587-1, IEC 61587-2	Ocel	Ocel	Cabinet/Rack Frame	1600 kgf

Katalogové číslo	Kód barvy	Complies With	Frame Material	Materiál	Product Type	Static Load
20630-272	RAL 7021	IEC 61587-1, IEC 61587-2	Ocel	Ocel	Cabinet/Rack Frame	1600 kgf
20630-273	RAL 7021	IEC 61587-1, IEC 61587-2	Ocel	Ocel	Cabinet/Rack Frame	1600 kgf
20630-274	RAL 7021	IEC 61587-1, IEC 61587-2	Ocel	Ocel	Cabinet/Rack Frame	1600 kgf
20630-275	RAL 7021	IEC 61587-1, IEC 61587-2	Ocel	Ocel	Cabinet/Rack Frame	1600 kgf
20630-276	RAL 7021	IEC 61587-1, IEC 61587-2	Ocel	Ocel	Cabinet/Rack Frame	1600 kgf
20630-277	RAL 7021	IEC 61587-1, IEC 61587-2	Ocel	Ocel	Cabinet/Rack Frame	1600 kgf
20630-278	RAL 7021	IEC 61587-1, IEC 61587-2	Ocel	Ocel	Cabinet/Rack Frame	1600 kgf
20630-279	RAL 7021	IEC 61587-1, IEC 61587-2	Ocel	Ocel	Cabinet/Rack Frame	1600 kgf
20630-280	RAL 7021	IEC 61587-1, IEC 61587-2	Ocel	Ocel	Cabinet/Rack Frame	1600 kgf
20630-281	RAL 7021	IEC 61587-1, IEC 61587-2	Ocel	Ocel	Cabinet/Rack Frame	1600 kgf
20630-282	RAL 7021	IEC 61587-1, IEC 61587-2	Ocel	Ocel	Cabinet/Rack Frame	1600 kgf
20630-283	RAL 7021	IEC 61587-1, IEC 61587-2	Ocel	Ocel	Cabinet/Rack Frame	1600 kgf
20630-284	RAL 7021	IEC 61587-1, IEC 61587-2	Ocel	Ocel	Cabinet/Rack Frame	1600 kgf
20630-285	RAL 7021	IEC 61587-1, IEC 61587-2	Ocel	Ocel	Cabinet/Rack Frame	1600 kgf
20630-286	RAL 7021	IEC 61587-1, IEC 61587-2	Ocel	Ocel	Cabinet/Rack Frame	1600 kgf
20630-287	RAL 7021	IEC 61587-1, IEC 61587-2	Ocel	Ocel	Cabinet/Rack Frame	1600 kgf
20630-288	RAL 7021	IEC 61587-1, IEC 61587-2	Ocel	Ocel	Cabinet/Rack Frame	1600 kgf

Table 3/3

Katalogové číslo	Typ	Works With
------------------	-----	------------

20630-269	Heavy Load	Varistar CP
20630-270	Heavy Load	
20630-271	Heavy Load	Varistar CP
20630-272	Heavy Load	Varistar CP
20630-273	Heavy Load	Varistar CP
20630-274	Heavy Load	Varistar CP
20630-275	Heavy Load	Varistar CP
20630-276	Heavy Load	Varistar CP
20630-277	Heavy Load	Varistar CP
20630-278	Heavy Load	Varistar CP
20630-279	Heavy Load	Varistar CP
20630-280	Heavy Load	Varistar CP
20630-281	Heavy Load	Varistar CP
20630-282	Heavy Load	Varistar CP
20630-283	Heavy Load	Varistar CP
20630-284	Heavy Load	Varistar CP
20630-285	Heavy Load	Varistar CP
20630-286	Heavy Load	Varistar CP
20630-287	Heavy Load	Varistar CP

20630-288	Heavy Load	Varistar CP
-----------	------------	-------------

DALŠÍ PODROBNOSTI O PRODUKTU

Please order attachments and components separately.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE